

IB ST 24 DO32/2-WT - I/O module

2752482

<https://www.phoenixcontact.com/us/products/2752482>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS-ST digital output module, 32 outputs, 24 V DC, 500 mA, 2-conductor connection technology, IP20 degree of protection, consisting of: terminal part with screw connection and module electronics, extended temperature range

Commercial data

Item number	2752482
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI332
GTIN	4017918272449
Weight per piece (including packing)	759.3 g
Weight per piece (excluding packing)	741 g
Customs tariff number	85389091
Country of origin	DE

IB ST 24 DO32/2-WT - I/O module

2752482

<https://www.phoenixcontact.com/us/products/2752482>



Technical data

Dimensions

Width	118 mm
Height	117 mm
Length	116 mm

Interfaces

ST local bus

Connection method	INTERBUS-ST local bus
Transmission speed	500 kbps

Output data

Digital

Number of outputs	32
Output voltage	$U_S - 1\text{ V}$
Protective circuit	Short-circuit protection of outputs; Electronic per channel

Product properties

Product type	I/O component
Product family	Smart Terminal ST
Type	modular

Electrical properties

Test section	Bus/Output groups 500 V AC 50 Hz 1 min
	Output groups/Ground conductor 500 V AC 50 Hz 1 min
	Output group/Output group 500 V AC 50 Hz 1 min

Supply

Communications power U_L	9 V DC (from the ST local bus)
I/O voltage	24 V DC
I/O voltage range	20 V DC ... 30 V DC
Residual ripple	$\pm 1.2\text{ V}_{PP}$
Typical current consumption	100 mA (from the ST local bus)

Connection data

Conductor connection

Connection method	Screw connection
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	8 mm
Connection method	Screw connection

IB ST 24 DO32/2-WT - I/O module



2752482

<https://www.phoenixcontact.com/us/products/2752482>

Conductor cross-section, rigid	0.2 mm² ... 2.5 mm²
Conductor cross-section, flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section AWG	24 ... 12
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB ST 24 DO32/2-WT - I/O module

2752482

<https://www.phoenixcontact.com/us/products/2752482>



Classifications

UNSPSC

UNSPSC 21.0	32151602
-------------	----------

IB ST 24 DO32/2-WT - I/O module

2752482

<https://www.phoenixcontact.com/us/products/2752482>



Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com