

CB TM2 6A SFB P - Thermal-magnetic device circuit breaker



2800874

<https://www.phoenixcontact.com/us/products/2800874>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal-magnetic device circuit breaker, 2-pos., tripping characteristic SFB, 2 changeover contacts, plug for base element.

Product description

Thermal-magnetic device circuit breaker

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2800874       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL04          |
| Product key                          | CLA124        |
| GTIN                                 | 4046356690393 |
| Weight per piece (including packing) | 70.6 g        |
| Weight per piece (excluding packing) | 68.9 g        |
| Customs tariff number                | 85362010      |
| Country of origin                    | ID            |

# CB TM2 6A SFB P - Thermal-magnetic device circuit breaker



2800874

<https://www.phoenixcontact.com/us/products/2800874>

## Technical data

### Notes

|         |                                                                                                               |
|---------|---------------------------------------------------------------------------------------------------------------|
| General | When mounted in rows, the nominal device current can be limited to just 80% or must be oversized accordingly. |
|---------|---------------------------------------------------------------------------------------------------------------|

### Product properties

|                     |                                        |
|---------------------|----------------------------------------|
| Product type        | Thermomagnetic device circuit breakers |
| Product family      | CB TM                                  |
| Type                | Male                                   |
| Number of positions | 2                                      |
| No. of channels     | 1                                      |

### Insulation characteristics

|                     |   |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

### Electrical properties

|           |                  |
|-----------|------------------|
| Fuse type | Automatic device |
|-----------|------------------|

### General

|                                                 |                                                                     |
|-------------------------------------------------|---------------------------------------------------------------------|
| Rated voltage                                   | 80 V DC (IEC 60934)                                                 |
|                                                 | 80 V DC (UL 1077)                                                   |
|                                                 | 80 V DC (UL 508 - with plug-in base)                                |
| Rated insulation voltage $U_i$                  | 277 V AC (UL 1077)                                                  |
|                                                 | 250 V AC (IEC 60934)                                                |
| Rated current $I_N$                             | 6 A (IEC 60934)                                                     |
|                                                 | inductive load according to UL 1077                                 |
|                                                 | 6 A DC (low-induction load according to UL 1077)                    |
|                                                 | 6 A DC (inductive load according to UL 508 - with plug-in base)     |
|                                                 | 6 A DC (low-induction load according to UL 508 - with plug-in base) |
| Rated surge voltage                             | 2.5 kV (Increased insulation in actuation area)                     |
| Insulation resistance $R_{iso}$                 | > 100 M $\Omega$ (500 V DC)                                         |
| Auxiliary circuit                               | 277 V AC / 0.5 A (Low-induction)                                    |
|                                                 | 277 V AC / 1 A (Low-induction, maximum of 2000 cycles)              |
|                                                 | 50 V DC / 1 A (Low-induction)                                       |
| Type of actuation                               | S type                                                              |
| Tripping method                                 | TM (thermal-magnetic)                                               |
| Tripping level                                  | Trip-free mechanism (positive)                                      |
| Device resistance                               | 50 m $\Omega$                                                       |
| Required backup fuse                            | $\geq 24$ A ( $I > I_{cn}$ )                                        |
| Rated short-circuit switching capacity $I_{cn}$ | 600 A (80 V DC)                                                     |
| Short-circuit switching capacity                | 1000 A AC (277 V AC)                                                |
|                                                 | 1000 A DC (50 V DC)                                                 |
|                                                 | 3000 V AC (Actuation area)                                          |

# CB TM2 6A SFB P - Thermal-magnetic device circuit breaker



2800874

<https://www.phoenixcontact.com/us/products/2800874>

|                        |                                          |
|------------------------|------------------------------------------|
| Dielectric strength    | 1500 V AC (Main to auxiliary circuit)    |
|                        | 1500 V AC (Open main circuit)            |
|                        | 1000 V AC (Open auxiliary circuit)       |
|                        | 1500 V AC (Position to position)         |
| Switching cycles, max. | 6000 (240 V AC / 1 x I <sub>n</sub> )    |
|                        | 3000 (80 V DC/1 x I <sub>n</sub> )       |
| Fuse                   | SFB                                      |
| Power dissipation      | 1.8 W (in nominal operation per channel) |
| Voltage drop           | 0.29 V (at 1 x I <sub>n</sub> )          |
| Contact switching type | 2 changeover contacts                    |


## Auxiliary contact

|                                               |       |
|-----------------------------------------------|-------|
| Minimum operating voltage U <sub>min</sub> DC | 10 V  |
| Maximum operating voltage U <sub>max</sub> DC | 240 V |
| Maximum operating voltage U <sub>max</sub> AC | 240 V |
| Minimum operating current I <sub>min</sub>    | 10 mA |
| Max. operating current I <sub>max</sub>       | 1 A   |

## Connection data

|                   |           |
|-------------------|-----------|
| Connection method | pluggable |
| Connection method | pluggable |

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 24.6 mm                                                                              |
| Height              | 45 mm                                                                                |
| Depth               | 52 mm                                                                                |

## Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | gray (RAL 7042)  |
|                                        | black (RAL 9005) |
| Flammability rating according to UL 94 | V-0              |
| Insulating material group              | II               |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Environmental and real-life conditions

# CB TM2 6A SFB P - Thermal-magnetic device circuit breaker



2800874

<https://www.phoenixcontact.com/us/products/2800874>

## Ambient conditions

|                                         |                               |
|-----------------------------------------|-------------------------------|
| Degree of protection                    | IP30 (Actuation area)         |
| Ambient temperature (operation)         | -30 °C ... 60 °C              |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C              |
| Humidity test                           | 240 h, 95 % RH, 40 °C         |
| Shock (operation)                       | 30g (IEC 60068-2-27, Test Ea) |
| Vibration (operation)                   | 8g (IEC 60068-2-6, Test Fc)   |

## Approvals

### UL approval

|                |                            |
|----------------|----------------------------|
| Identification | UL Listed UL 508           |
|                | UL/C-UL Recognized UL 1077 |

### CSA

|                |                              |
|----------------|------------------------------|
| Identification | CSA CAN/CSA-C22.2 No. 235-04 |
|----------------|------------------------------|

### Shipbuilding approval

|                |        |
|----------------|--------|
| Identification | DNV GL |
|----------------|--------|

## Standards and regulations

|                          |          |
|--------------------------|----------|
| Standards/specifications | EN 60934 |
|--------------------------|----------|

## Mounting

|               |                 |
|---------------|-----------------|
| Mounting type | on base element |
|---------------|-----------------|


# CB TM2 6A SFB P - Thermal-magnetic device circuit breaker

2800874

<https://www.phoenixcontact.com/us/products/2800874>


## Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Application drawing




The figure shows the single-position versions

# CB TM2 6A SFB P - Thermal-magnetic device circuit breaker


2800874

<https://www.phoenixcontact.com/us/products/2800874>

Application drawing



Diagram



Trigger characteristic in the DC range


# CB TM2 6A SFB P - Thermal-magnetic device circuit breaker



2800874

<https://www.phoenixcontact.com/us/products/2800874>

Circuit diagram



# CB TM2 6A SFB P - Thermal-magnetic device circuit breaker



2800874

<https://www.phoenixcontact.com/us/products/2800874>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2800874>



**cUL Recognized**  
Approval ID: FILE E 140459



**UL Recognized**  
Approval ID: FILE E 140459



**DNV GL**  
Approval ID: TAE00003C7



**VDE Zeichengenehmigung**  
Approval ID: 40034683



**CCC**  
Approval ID: 2025010307749779



**CSA**  
Approval ID: 2786957



**KC**  
Approval ID: SW05012-15004

**UAE-RoHS**

Approval ID: 22-09-50938



2800874  
<https://www.phoenixcontact.com/us/products/2800874>

Classifications

ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140401 |
| ECLASS-15.0 | 27140401 |

ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC003538 |
|----------|----------|

UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

2800874  
<https://www.phoenixcontact.com/us/products/2800874>

Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.0 Climate Change                    |                                          |
| CO2e kg                                 | 9.042 kg CO2e                            |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)