

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in relay interface for protection against interference on the control side, with soldered-in miniature switching relay, contacts (Au): small loads, 1 changeover contact, input voltage 24 V AC/DC

Your advantages

- Use of AC output cards, resulting in residual AC currents
- Resistant to interference currents
- Applications with long control lines
- High relay release voltage

Commercial data

Item number	2826981
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6121
GTIN	4017918078034
Weight per piece (including packing)	41 g
Weight per piece (excluding packing)	41 g
Customs tariff number	85364190
Country of origin	DE

Technical data

Product properties

Product type	Relay Module
Mechanical service life	approx. 2×10^7 cycles

Insulation characteristics

Insulation	Basic insulation
Overtoltage category	III
Pollution degree	2

Data management status

Date of last data management	12.09.2025
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.62 W
Test voltage (Winding/contact)	2.5 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U_N	24 V AC
Input voltage range	21.6 V AC ... 26.4 V AC
Input voltage range in reference to U_N	0.9 ... 1.1
Drive and function	monostable
Typical input current at U_N	26 mA
Typical response time	8 ms (with DC)
Typical release time	10 ms (with DC)
Protective circuit	Bridge rectifier; Bridge rectifier
	Surge protection; Varistor
	RC element; RC element
Operating voltage display	Yellow LED

Output data

Switching

Contact switching type	Double contact, 1 changeover contact
Type of switch contact	Double contact
Contact material	Au
Maximum switching voltage	30 V AC
	36 V DC
Limiting continuous current	0.5 A
Maximum inrush current	0.2 A
Interrupting rating (ohmic load) max.	5 W

Dimensions

ST-REL3-KG 24/21/AU/SO46 - Relay connectors

2826981

<https://www.phoenixcontact.com/us/products/2826981>



Width	20.8 mm
Height	42.5 mm
Depth	112 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

Mounting


Mounting type	Plug-in mounting
Mounting position	any

2826981

<https://www.phoenixcontact.com/us/products/2826981>

Drawings

Circuit diagram



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com