

UM-2KS50/DI32/CS/SO180 - Passive module



2901013

<https://www.phoenixcontact.com/us/products/2901013>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



32-channel digital input module with screw connection and redundant voltage supply. Suitable for Yokogawa ADV151 and ADV161 cards.

Commercial data

Item number	2901013
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK218N
GTIN	4046356560085
Weight per piece (including packing)	718.2 g
Weight per piece (excluding packing)	569.6 g
Country of origin	DE

UM-2KS50/DI32/CS/SO180 - Passive module



2901013

<https://www.phoenixcontact.com/us/products/2901013>

Technical data

Product properties

Product type	Interface module
No. of channels	32

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V DC ± 10 %
Max. current carrying capacity per branch	100 mA
Rated surge voltage	0.5 kV

Supported controller YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV151
	ADV161

Supported controller YOKOGAWA STARDOM

Suitable I/O card	NFDV151
	NFDV161

Connection data

Field level

Connection method	Screw connection
Number of positions	32
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 14

Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50
Note	Usable system cables: Phoenix Contact YUC50, Yokogawa AKB331
Tightening torque	0.5 Nm

Supply

Connection method	Screw connection
Number of connections	1
Number of positions	6
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²

UM-2KS50/DI32/CS/SO180 - Passive module



2901013

<https://www.phoenixcontact.com/us/products/2901013>

Conductor cross-section AWG	24 ... 14
-----------------------------	-----------

HART connector

Connection method	HART connector
-------------------	----------------

Signaling

Status display present	yes
------------------------	-----

Dimensions

Item dimensions

Width	139.5 mm
Height	125.4 mm
Depth	65.8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	Voltage monitoring on the module does not work in combination with upstream HESILED fuse terminal blocks with integrated LED display.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

UM-2KS50/DI32/CS/SO180 - Passive module




2901013


<https://www.phoenixcontact.com/us/products/2901013>

Drawings

Dimensional drawing



Circuit diagram



UM-2KS50/DI32/CS/SO180 - Passive module



2901013

<https://www.phoenixcontact.com/us/products/2901013>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901013>



EAC

Approval ID: RU*-DE.*08.B.01829*

UM-2KS50/DI32/CS/SO180 - Passive module



2901013

<https://www.phoenixcontact.com/us/products/2901013>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2901013

<https://www.phoenixcontact.com/us/products/2901013>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com