

VIP-3/PT/FLK26/LED - Termination board

2904252

<https://www.phoenixcontact.com/us/products/2904252>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 26-pos., with LED

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2904252 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C423 |
| Product key | DK2121 |
| GTIN | 4046356813631 |
| Weight per piece (including packing) | 154.4 g |
| Weight per piece (excluding packing) | 154.1 g |
| Customs tariff number | 85366990 |
| Country of origin | US |

VIP-3/PT/FLK26/LED - Termination board

2904252

<https://www.phoenixcontact.com/us/products/2904252>



Technical data

Product properties

| | |
|---------------------|------------------------|
| Product type | Interface module |
| Product family | VARIOFACE Professional |
| Number of positions | 26 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|---------|
| Nominal voltage U_N | 24 V DC |
| Max. current carrying capacity per branch | 1 A |

Connection data

Field level

| | |
|----------------------------------|--|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 26 ... 14 |

Controller level

| | |
|-----------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 26 |
| Pitch | 2.54 mm |

Signaling

| | |
|------------------------|-----|
| Status display | LED |
| Status display present | yes |

Dimensions

Item dimensions

| | |
|--------|---------|
| Width | 57.1 mm |
| Height | 75.8 mm |
| Depth | 63 mm |

Material specifications

| | |
|--|-----------------------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Housing insulation material | Polyamide PA non-reinforced |

VIP-3/PT/FLK26/LED - Termination board

2904252

<https://www.phoenixcontact.com/us/products/2904252>



Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |

Mounting


| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

Drawings

Circuit diagram



VIP-3/PT/FLK26/LED - Termination board

2904252

<https://www.phoenixcontact.com/us/products/2904252>



Classifications

UNSPSC

UNSPSC 21.0

39121432

VIP-3/PT/FLK26/LED - Termination board

2904252

<https://www.phoenixcontact.com/us/products/2904252>



Environmental product compliance

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com