

# EMG 22-DIO 7P - Diode block

2950064

<https://www.phoenixcontact.com/us/products/2950064>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Diode module, for extension with 7 1N 4007 diodes, common cathode



## Your advantages

- Electrical decoupling of messages in fault reporting systems
- Spark-suppression diodes for limiting surge voltages of inductive loads

## Commercial data

Item number	2950064
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK66M1
GTIN	4017918083939
Weight per piece (including packing)	44.95 g
Weight per piece (excluding packing)	44.95 g
Customs tariff number	85411000
Country of origin	DE

# EMG 22-DIO 7P - Diode block

2950064

<https://www.phoenixcontact.com/us/products/2950064>



## Technical data

### Product properties

Product type	Diode module
Insulation characteristics	
Pollution degree	2

### Input data

Diode	
Description of the input	7 diodes, common cathode
Diode type	1 N 4007
Max. operating voltage $U_{max}$	250 V AC
Peak reverse voltage per diode	1300 V
Reverse current per diode	5 $\mu$ A
Conducting state voltage per diode	approx. 0.8 V
Conducting state current per diode	0.7 A (with single load)
	0.5 A (with simultaneous loads)

### Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Dimensions

Width	22.5 mm
Height	75 mm
Depth	55 mm

### Material specifications

Color	green (RAL 6021)
-------	------------------

### Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

### Approvals

CE	
Certificate	CE-compliant

# EMG 22-DIO 7P - Diode block

2950064

<https://www.phoenixcontact.com/us/products/2950064>



Note

and EN 61326

## Standards and regulations

Standards/regulations

DIN EN 50178

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# EMG 22-DIO 7P - Diode block


2950064

<https://www.phoenixcontact.com/us/products/2950064>



## Drawings

Circuit diagram



# EMG 22-DIO 7P - Diode block

2950064

<https://www.phoenixcontact.com/us/products/2950064>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2950064>



**EAC**

Approval ID: RU C-DE.A\*30.B.01082



**EAC**

Approval ID: RU\*DE\*08.B.01841/19

# EMG 22-DIO 7P - Diode block

2950064

<https://www.phoenixcontact.com/us/products/2950064>



## Classifications

### ECLASS

ECLASS-13.0	27371010
ECLASS-15.0	27371010

### ETIM

ETIM 9.0	EC000683
----------	----------

### UNSPSC

UNSPSC 21.0	32151500
-------------	----------

# EMG 22-DIO 7P - Diode block

2950064

<https://www.phoenixcontact.com/us/products/2950064>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b36e43dd-de9d-42ce-836e-5657674eb4a0

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)