

# ST 2,5-QUATTRO-DIO/L-R OG - Component terminal block



3028937

<https://www.phoenixcontact.com/us/products/3028937>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component terminal block, with integrated diode, nom. voltage: 800 V, nominal current: 0.5 A, connection method: Spring-cage connection, Rated cross section: 1 mm<sup>2</sup>, cross section: 0.08 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting: NS 35/7,5, NS 35/15, color: orange

## Commercial data

Item number	3028937
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE02
Product key	BE2171
GTIN	4017918927868
Weight per piece (including packing)	9.81 g
Weight per piece (excluding packing)	9.81 g
Customs tariff number	85369010
Country of origin	PL

# ST 2,5-QUATTRO-DIO/L-R OG - Component terminal block



3028937

<https://www.phoenixcontact.com/us/products/3028937>

## Technical data

### Product properties

Product type	Component terminal block
Number of connections	4
Number of rows	1
Potentials	1

### Insulation characteristics

Overshoot category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	0.77 W

### Connection data

Number of connections per level	4
Nominal cross section	2.5 mm <sup>2</sup>
Connection method	Spring-cage connection
Stripping length	8 mm ... 10 mm
Internal cylindrical gage	A3
Conductor cross-section rigid	0.08 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Cross section AWG	28 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.08 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	28 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm <sup>2</sup>
Nominal current	0.5 A
Maximum load current	0.5 A (the maximum current is determined by the diode)
Nominal voltage	800 V
Nominal cross section	1 mm <sup>2</sup>

### Dimensions

Width	5.2 mm
End cover width	2.2 mm

### Material specifications

Color	orange (RAL 2003)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

# ST 2,5-QUATTRO-DIO/L-R OG - Component terminal block



3028937

<https://www.phoenixcontact.com/us/products/3028937>

## Mechanical properties

### Mechanical data

Open side panel	Yes
-----------------	-----

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

## Mounting

Mounting type	NS 35/7,5
	NS 35/15

# ST 2,5-QUATTRO-DIO/L-R OG - Component terminal block



3028937

<https://www.phoenixcontact.com/us/products/3028937>

## Classifications

### ETIM

ETIM 8.0

EC000903

### UNSPSC

UNSPSC 21.0

39121400

# ST 2,5-QUATTRO-DIO/L-R OG - Component terminal block



3028937

<https://www.phoenixcontact.com/us/products/3028937>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50  An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	44a2530b-119a-496f-8cd5-7454414071b8

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)