

FLKM-D50 SUB/S - Termination board

2281157

<https://www.phoenixcontact.com/us/products/2281157>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and D-Subminiature pin strip, for mounting on NS 35/7.5 or NS 32, 50-pos.

Commercial data

Item number	2281157
Packing unit	5 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2182
GTIN	4017918054601
Weight per piece (including packing)	236.1 g
Weight per piece (excluding packing)	236.1 g
Customs tariff number	85369010
Country of origin	DE

FLKM-D50 SUB/S - Termination board



2281157

<https://www.phoenixcontact.com/us/products/2281157>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 2.5 A
Current (Total current)	≤ 90 A

Air clearances and creepage distances

Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (1.2/50 µs)

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60807-2
Connection method	D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	50
Insertion/withdrawal cycles	> 500
Pitch	2.77 mm

Connection 2 (field level)

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Number of positions	34
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
	0.25 mm ² ... 1.5 mm ² (Ferrule without plastic sleeve)
	0.25 mm ² ... 2.5 mm ² (Ferrule with plastic sleeve)
Conductor cross-section flexible (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ²
	0.25 mm ² ... 0.75 mm ² (Ferrule without plastic sleeve)

FLKM-D50 SUB/S - Termination board



2281157

<https://www.phoenixcontact.com/us/products/2281157>

Conductor cross-section AWG	0.5 mm ² ... 0.5 mm ² (TWIN ferrule with plastic sleeve)
Tightening torque	24 ... 12
Pitch	0.5 Nm ... 0.6 Nm
	5.08 mm

Connection 3 (field level)

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	18
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
	0.25 mm ² ... 2.5 mm ² (Ferrule without plastic sleeve)
	0.25 mm ² ... 2.5 mm ² (Ferrule with plastic sleeve)
Conductor cross-section flexible (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ²
	0.25 mm ² ... 0.75 mm ² (Ferrule without plastic sleeve)
	0.5 mm ² ... 1.5 mm ² (TWIN ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm
Pitch	5.08 mm

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions	
Width	112.5 mm
Height	77 mm
Depth	57.47 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide 6 green

Environmental and real-life conditions

Ambient conditions	
Degree of protection (Module)	IP20
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

FLKM-D50 SUB/S - Termination board



2281157

<https://www.phoenixcontact.com/us/products/2281157>

Approvals

UKCA

Certificate

UKCA-compliant

Standards and regulations

Air clearances and creepage distances

Standards/regulations

EN IEC 60664-1

Mounting

Mounting type

DIN rail mounting

Assembly note

in rows with zero spacing

Mounting position

any

Notes

Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

FLKM-D50 SUB/S - Termination board


2281157

<https://www.phoenixcontact.com/us/products/2281157>



Drawings

Schematic diagram




FLKM-D50 SUB/S - Termination board

2281157

<https://www.phoenixcontact.com/us/products/2281157>



Circuit diagram



FLKM-D50 SUB/S - Termination board



2281157

<https://www.phoenixcontact.com/us/products/2281157>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2281157>

cUL Recognized		Approval ID: E118976		
		Nominal voltage U_N	Nominal current I_N	Cross section AWG
keine				
Field wiring		125 V	2.5 A	30 - 12

UL Recognized		Approval ID: E118976		
		Nominal voltage U_N	Nominal current I_N	Cross section AWG
keine				
Field wiring		125 V	2.5 A	30 - 12

FLKM-D50 SUB/S - Termination board

2281157

<https://www.phoenixcontact.com/us/products/2281157>



Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLKM-D50 SUB/S - Termination board

2281157

<https://www.phoenixcontact.com/us/products/2281157>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com