

# FB-HSB-DP-SC - Repeater

2316382

<https://www.phoenixcontact.com/us/products/2316382>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PROFIBUS DP coupler system for integration and diagnostics of PROFIBUS DP. Includes the one-network head station unit (FB-HSB), PROFIBUS DP repeater with oscilloscope (FB-DP-RPTR/SC).

## Product description

PROFIBUS head station with a PROFIBUS DP repeater provides network diagnostics and an oscilloscope feature.

## Your advantages

- Powerful, embedded web server for configuration and access to network diagnostics
- Manage and configure PROFIBUS field devices using FDT/DTM
- One communication interface module can drive up to ten individual PROFIBUS DP or PROFIBUS PA modules
- Auto detect any baud rate up to 12 Mbps transparently

## Commercial data

Item number	2316382
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DN11
Product key	DNC135
GTIN	4055626287973
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85176200
Country of origin	NL

# FB-HSB-DP-SC - Repeater

2316382

<https://www.phoenixcontact.com/us/products/2316382>



Set consists of

## FB-DP-RPTR/SC - Repeater

2316374

<https://www.phoenixcontact.com/us/products/2316374>

PROFIBUS DP interface/repeater module with oscilloscope functionality



## FB-HSB - Converter

2316379

<https://www.phoenixcontact.com/us/products/2316379>

Head station for monitoring one PROFIBUS network



# FB-HSB-DP-SC - Repeater

2316382

<https://www.phoenixcontact.com/us/products/2316382>



## Technical data

### Notes

Note on application

Note on application

Only for industrial use

### Product properties

Product type

Device coupler

### Electrical properties

#### Supply

Supply voltage range

10.8 V DC ... 26.4 V DC

Max. current consumption

800 mA

### Connection data

#### Supply

Conductor cross-section, flexible

0.20 mm<sup>2</sup> ... 2.50 mm<sup>2</sup>

Conductor cross-section, rigid

0.20 mm<sup>2</sup> ... 2.50 mm<sup>2</sup>

Conductor cross-section AWG

24 ... 12

### Interfaces

#### Data: Ethernet

Connection method

RJ45

No. of channels

1

Conductor cross-section flexible max.

2.5 mm<sup>2</sup>

Conductor cross-section flexible min.

0.2 mm<sup>2</sup>

Conductor cross-section, rigid max.

2.5 mm<sup>2</sup>

Conductor cross-section, rigid min.

0.2 mm<sup>2</sup>

Conductor cross-section AWG max.

12

Conductor cross-section AWG min.

24

### Material specifications

Color

green

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection

IP20

Ambient temperature (operation)

-20 °C ... 60 °C

Ambient temperature (storage/transport)

-20 °C ... 60 °C

Permissible humidity (operation)

5 % ... 95 % (non-condensing)

Permissible humidity (storage/transport)

5 % ... 95 % (non-condensing)

# FB-HSB-DP-SC - Repeater

2316382

<https://www.phoenixcontact.com/us/products/2316382>



## Approvals

### Conformity/Approvals

UL, USA / Canada	UL 508 Listed
UL, Canada	CSA C22.2 No. 142

## Standards and regulations

### Standards/regulations

Standards/regulations	Ring wave noise immunity in acc. with IEC 61000-4-12
-----------------------	--

### Standards/regulations

Standards/regulations	Dry heat in acc. with IEC 61131-2
-----------------------	-----------------------------------

### Standards/regulations

Standards/regulations	Damp heat in acc. with IEC 61131-2
-----------------------	------------------------------------

### Standards/regulations

Standards/regulations	Shock and vibration in acc. with EN 61131-2 and EN 50178
-----------------------	--

### PROFIBUS standardization

Standards/regulations	IEC 61158-2
-----------------------	-------------

## Mounting

### Mounting type

Mounting type	DIN rail: 35 mm
---------------	-----------------

### Mounting position

# FB-HSB-DP-SC - Repeater

2316382

<https://www.phoenixcontact.com/us/products/2316382>



## Classifications

### ECLASS

ECLASS-13.0	27242608
-------------	----------

### ETIM

ETIM 9.0	EC001604
----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# FB-HSB-DP-SC - Repeater

2316382

<https://www.phoenixcontact.com/us/products/2316382>



## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)