

# VIP-3/SC/D25SUB/F/LED - Termination board

2322210

<https://www.phoenixcontact.com/us/products/2322210>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and D-Subminiature socket strip, for mounting on NS 35 rails, with LED, 25-pos.

## Your advantages

- 9-pos. ... 50-pos.
- Metal foot
- In accordance with IEC 60603-13
- Screw connection
- 1:1 connection
- Screw connection

## Commercial data

Item number	2322210
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK2112
GTIN	4046356451833
Weight per piece (including packing)	132.3 g
Weight per piece (excluding packing)	152.3 g
Customs tariff number	85366990
Country of origin	US

# VIP-3/SC/D25SUB/F/LED - Termination board

2322210

<https://www.phoenixcontact.com/us/products/2322210>



## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	25

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	2.5 A

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

#### Controller level

Connection method	D-SUB socket strip
Number of connections	1
Number of positions	25

### Signaling

Status display	LED
Status display present	yes

### Dimensions

#### Item dimensions

Width	57.4 mm
Height	69 mm
Depth	62 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

# VIP-3/SC/D25SUB/F/LED - Termination board

2322210

<https://www.phoenixcontact.com/us/products/2322210>



Housing insulation material

Polyamide PA non-reinforced

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-3/SC/D25SUB/F/LED - Termination board


2322210

<https://www.phoenixcontact.com/us/products/2322210>

**PHÖNIX CONTACT**

## Drawings

## Circuit diagram



# VIP-3/SC/D25SUB/F/LED - Termination board

2322210

<https://www.phoenixcontact.com/us/products/2322210>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2322210>

		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		24 V	2 A	28 - 12	-

		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		24 V	2 A	30 - 12	-

		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		24 V	2 A	30 - 12	-

		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		24 V	2 A	28 - 12	-

# VIP-3/SC/D25SUB/F/LED - Termination board

2322210

<https://www.phoenixcontact.com/us/products/2322210>



## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VIP-3/SC/D25SUB/F/LED - Termination board

2322210

<https://www.phoenixcontact.com/us/products/2322210>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9b4c625b-bb9b-4ef6-8020-a637996d5e9c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)