

# A 1,5 -12 - Ferrule



3202588

<https://www.phoenixcontact.com/us/products/3202588>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule, Length contact range: 12 mm, sleeve length: 12 mm, color: silver-colored



## Your advantages

- The insulation reliability of close connections is increased and the splicing of wires is prevented
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

## Commercial data

Item number	3202588
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Sales key	BH34
Product key	BH3412
GTIN	4017918161736
Weight per piece (including packing)	0.1 g
Weight per piece (excluding packing)	0.1 g
Customs tariff number	85369010
Country of origin	DE

# A 1,5 -12 - Ferrule



3202588

<https://www.phoenixcontact.com/us/products/3202588>

## Technical data

### Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	UL certified Made from soft tin-plated electrolytic copper Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size Long/short-term temperature: +105°C/+120°C

### Connection data

#### Conductor connection

Conductor cross-section flexible max.	1.5 mm <sup>2</sup>
Conductor cross-section AWG max.	16
Stripping length	12 mm

### Dimensions

Dimensional drawing	
Sleeve length	12 mm
Length contact range	12 mm
Maximum stripping length	12 mm
Ferrule diameter	1.7 mm
Sleeve wall thickness	0.15 mm
Inner dimensions of the insulating collar	2.8 mm

### Material specifications

Color	silver-colored
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Mechanical properties

Technical data	
Sleeve length	12 mm

### Environmental and real-life conditions

# A 1,5 -12 - Ferrule



3202588

<https://www.phoenixcontact.com/us/products/3202588>

## Ambient conditions

Permanent temperature	105 °C
Short-term temperature	120 °C

## Standards and regulations

Design according to standard	DIN 46228-1, UL 486F-A
------------------------------	------------------------


# A 1,5 -12 - Ferrule

3202588

<https://www.phoenixcontact.com/us/products/3202588>

## Drawings

Dimensional drawing



Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

# A 1,5 -12 - Ferrule



3202588

<https://www.phoenixcontact.com/us/products/3202588>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3202588>



**cULus Listed**

Approval ID: E488001

# A 1,5 -12 - Ferrule

3202588

<https://www.phoenixcontact.com/us/products/3202588>



## Classifications

### ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# A 1,5 -12 - Ferrule

3202588

<https://www.phoenixcontact.com/us/products/3202588>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)