

RAD-SPL-2-N/N - Antenna splitter

2702293

<https://www.phoenixcontact.com/us/products/2702293>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna splitter, frequency range: 0.3 GHz ... 6 GHz, degree of protection: IP65, connection: 3 x N (female), suitable connection cable for the antenna connection (Item No. 2700677)



Product description

2-way distributor for antenna signals (antenna splitter), type N connector (female) on the two upper ends and type N (female) on the lower end

Commercial data

Item number	2702293
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNC6Z1
GTIN	4055626079073
Weight per piece (including packing)	80.9 g
Weight per piece (excluding packing)	69 g
Customs tariff number	85366910
Country of origin	CN

RAD-SPL-2-N/N - Antenna splitter

2702293

<https://www.phoenixcontact.com/us/products/2702293>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Coaxial adapter

Electrical properties

Frequency range

0.3 GHz ... 6 GHz

Connection data

Connection method

N (female)

Material specifications

Housing material

Brass (CuZn)

Environmental and real-life conditions

Ambient conditions

Degree of protection

IP65, when installed

Ambient temperature (operation)

-40 °C ... 100 °C

Ambient temperature (storage/transport)

-70 °C ... 100 °C

Mounting

Assembly note

Outdoors and indoors

Accessories required

RAD-SPL-2-N/N - Antenna splitter

2702293

<https://www.phoenixcontact.com/us/products/2702293>



Classifications

ECLASS

ECLASS-13.0	19070417
ECLASS-15.0	19070417

ETIM

ETIM 9.0	EC001135
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RAD-SPL-2-N/N - Antenna splitter

2702293

<https://www.phoenixcontact.com/us/products/2702293>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4496d276-47e7-4149-b007-2f6157a4f5d8

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com