

RFC DUAL-FAN - Fan



2730239

<https://www.phoenixcontact.com/us/products/2730239>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fan module for Remote Field Controllers RFC 430 ETH-IB / RFC 450 ETH-IB



Your advantages

- Power supply via RFC 4xx
- Maintenance-free operation
- Easy mounting
- Optimum heat exchange for RFC 4xx controllers

Commercial data

Item number	2730239
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR10
Product key	DRAABZ
GTIN	4017918818746
Weight per piece (including packing)	171.3 g
Weight per piece (excluding packing)	170.4 g
Customs tariff number	84145915
Country of origin	DE

RFC DUAL-FAN - Fan

2730239

<https://www.phoenixcontact.com/us/products/2730239>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Fan

Electrical properties

Maximum power dissipation for nominal condition

4.8 W

Supply

Supply voltage

24 V DC

Typical current consumption

typ. 200 mA

Dimensions

Width

85 mm

Height

25 mm

Depth

126 mm

Note on dimensions

The height stated refers to the unmounted state

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

0 °C ... 55 °C

RFC DUAL-FAN - Fan

2730239

<https://www.phoenixcontact.com/us/products/2730239>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2730239>



cULus Recognized

Approval ID: E140324

RFC DUAL-FAN - Fan

2730239

<https://www.phoenixcontact.com/us/products/2730239>



Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 9.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

RFC DUAL-FAN - Fan

2730239

<https://www.phoenixcontact.com/us/products/2730239>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cc35fbc2-c234-412b-9f17-8ee0dce88b8a

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com