

PSM-SET-FSMA/4-KT - FO connectors

2799720

<https://www.phoenixcontact.com/us/products/2799720>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO connectors, degree of protection: IP20, number of positions: 2, MM, material: Metal, cable outlet: straight



Your advantages

- Suitable for quick and easy field assembly or repair
- No bonding or polishing
- Flexible application, thanks to reusable connector
- Outstanding transmission properties
- Robust connector

Commercial data

Item number	2799720
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIAA
GTIN	4017918156053
Weight per piece (including packing)	33.6 g
Weight per piece (excluding packing)	27.2 g
Customs tariff number	85367000
Country of origin	PL

PSM-SET-FSMA/4-KT - FO connectors

2799720

<https://www.phoenixcontact.com/us/products/2799720>



Technical data

Product properties

Product type	Fiber optic connector (cable side)
Type	FSMA
Number of positions	2
Cable outlet	straight

Insulation characteristics

Ovvoltage category	I
Degree of pollution	2

Electrical properties

Attenuation	< 1.5 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

Dimensions

Mechanical characteristics

Ferrule diameter	3.20 mm
------------------	---------

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal

Cable/line

Cable type	Plastic-coated fiber
External cable diameter	2.2 mm ... 2.2 mm
Individual wire diameter	2.2 mm
Resistance to oil	yes
Flame resistance	yes

FO cable

Fiber	980/1000 µm
Fiber type	POF

Characteristics

Attenuation	< 1.5 dB (Insertion attenuation)
-------------	----------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

PSM-SET-FSMA/4-KT - FO connectors

2799720

<https://www.phoenixcontact.com/us/products/2799720>



Ambient temperature (assembly)	0 °C ... 50 °C
Resistance to oil	yes

Standards and regulations

Flame resistance	yes
Resistance to oil	yes

Mounting

Mounting type	For field assembly
---------------	--------------------

PSM-SET-FSMA/4-KT - FO connectors

2799720

<https://www.phoenixcontact.com/us/products/2799720>



Classifications

ECLASS

ECLASS-13.0	19170122
ECLASS-15.0	19170122

ETIM

ETIM 9.0	EC001122
----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

PSM-SET-FSMA/4-KT - FO connectors

2799720

<https://www.phoenixcontact.com/us/products/2799720>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com