


IB IL 24 TC-PAC - Analog module

2861360

<https://www.phoenixcontact.com/us/products/2861360>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline thermistor terminal, complete with accessories (connector and marking field), 2-conductor connection technology

Your advantages

- Connection for a thermistor
- Integrated switching output
- Maximum permissible load current: 500 mA
- Diagnostic and status indicators

Commercial data

Item number	2861360
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI143
GTIN	4017918894306
Weight per piece (including packing)	85.1 g
Weight per piece (excluding packing)	50 g
Customs tariff number	85389099
Country of origin	DE

IB IL 24 TC-PAC - Analog module


2861360

<https://www.phoenixcontact.com/us/products/2861360>



Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps
Transmission physics	Copper

System properties

Module

ID code (dec.)	190
ID code (hex)	BE
Length code (hex)	41
Length code (dec)	65
Process data channel	4 bit
Input address area	4 bit
Output address area	0 Byte
Register length	4 bit
Required parameter data	1 Byte
Required configuration data	4 Byte

Input data

Analog

Input name	Resistance sensor
Description of the input	Input for PTC thermistor
Number of inputs	1

IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

Connection method	Spring-cage connection
Connection technology	2-conductor
Sensor types (RTD) that can be used	PTC thermistor according to DIN 44081 or DIN 44082
Input filter time	typ. 10 ms
Nominal value of the current sources	max. 1.2 mA (for open-circuit voltage of < 8 V DC)
Linear resistance measuring range	2.7 k Ω ... 3.5 k Ω (Shutdown range, total resistance)
	50 Ω ... 2.25 k Ω (Operating range, total resistance)

Output data

Analog:

Connection method	Spring-cage connection
Connection technology	2-conductor
Number of outputs	1
Protective circuit	short-circuit and overload proof
Current output signal	500 mA (per output)
Voltage output signal	24 V DC ($U_S - 1$ V)
Load/output load voltage output	< 2.7 k Ω (Total resistance for output signal HIGH)

Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet

Electrical properties

Maximum power dissipation for nominal condition	0.6 W
---	-------

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 60 mA

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 500 mA

Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V analog supply (analog I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V analog supply (analog I/O)/functional ground	500 V AC, 50 Hz, 1 min
Test voltage: Thermistor / all other areas	1200 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Conductor connection

Connection method	Spring-cage connection
Conductor cross-section rigid	0.08 mm² ... 1.5 mm²
Conductor cross-section flexible	0.08 mm² ... 1.5 mm²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm² ... 1.5 mm²
Conductor cross-section, flexible	0.08 mm² ... 1.5 mm²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	-25 % ... 55 % (75% average, 85% seldom)
Permissible humidity (storage/transport)	-25 % ... 85 %

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 TC-PAC - Analog module


2861360

<https://www.phoenixcontact.com/us/products/2861360>




Drawings

Dimensional drawing



Connection diagram



IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

Classifications

ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

ETIM

ETIM 9.0	EC001596
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fd9be18a-16a8-4c03-b96c-8d8294d6c25b

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com