

# FL SFP FX SM - Media module

2891082

<https://www.phoenixcontact.com/us/products/2891082>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).

## Product description

Developed according to IEC 61850-3 (Ambient conditions)

## Your advantages

- Network structure according to IEC 61850
- IEEE 1613
- MSA compliant

## Commercial data

Item number	2891082
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN22
Product key	DNN612
GTIN	4046356800969
Weight per piece (including packing)	30.4 g
Weight per piece (excluding packing)	16 g
Customs tariff number	85176200
Country of origin	TW

# FL SFP FX SM - Media module

2891082

<https://www.phoenixcontact.com/us/products/2891082>



## Technical data

### Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Housing material	Metal
------------------	-------

### Mounting

Mounting type	Plug-in mounting (SFP port)
---------------	-----------------------------

### Interfaces

#### Ethernet FO

Connection method	1 LC socket at the SFP module, 100 Mbps
Transmission speed	100 Mbps
Minimum receiver sensitivity	-35 dBm
Maximum receiver sensitivity	-3 dBm
Transmission physics	Single-mode fiberglass
Transmission length	typ. 40 km
Wavelength	1310 nm
Signal LEDs	depending on the Factoryline device
No. of channels	1 (LC single mode)

### Product properties

Product type	SFP module
Type	Factoryline devices with SFP slot
Format	SFP (Small Form-factor Pluggable)
Basic functions	SFP module as FO port
	MSA compliant

### Signaling

Status display	via a Factoryline device
----------------	--------------------------

### Electrical properties

Maximum power dissipation for nominal condition	0.66 W (when installed)
Transmission medium	Single-mode fiberglass

### Supply

# FL SFP FX SM - Media module

2891082

<https://www.phoenixcontact.com/us/products/2891082>



Supply voltage	3.3 V (via Factoryline switch)
Power supply connection	via SFP slot

## Connection data

Connection method	To insert in SFP slot
-------------------	-----------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

## Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3

# FL SFP FX SM - Media module

2891082

<https://www.phoenixcontact.com/us/products/2891082>



## Approvals

>To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2891082>



**DNV GL**

Approval ID: TAA00000YV



**LR**

Approval ID: LR22250919TA



**NK**

Approval ID: TA24215M



**BV**

Approval ID: 48146\_B1 BV

**BSH**

Approval ID: Nr. 966



**RINA**

Approval ID: ELE014724XG001

**ABS**

Approval ID: 21\_2066186\_1\_PDA



**cULus Recognized**

Approval ID: E140403

# FL SFP FX SM - Media module

2891082

<https://www.phoenixcontact.com/us/products/2891082>



## Classifications

### ECLASS

ECLASS-13.0	19179090
ECLASS-15.0	19179090

### ETIM

ETIM 9.0	EC000310
----------	----------

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

# FL SFP FX SM - Media module

2891082

<https://www.phoenixcontact.com/us/products/2891082>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4d429d42-8850-4841-b291-c0aa50fcb10a

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)