

# VIP-2/SC/FLK50 - Passive module


2900463

<https://www.phoenixcontact.com/us/products/2900463>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE interface module



## Commercial data

Item number	2900463
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C423
Product key	DK2111
GTIN	4046356552875
Weight per piece (including packing)	284.2 g
Weight per piece (excluding packing)	279.5 g
Customs tariff number	85366990
Country of origin	US

# VIP-2/SC/FLK50 - Passive module

2900463

<https://www.phoenixcontact.com/us/products/2900463>



## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	50

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M 3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

### Signaling

Status display	no
Status display present	no

### Dimensions

#### Item dimensions

Width	131.5 mm
Height	65.5 mm
Depth	56 mm

### Material specifications

Color	gray (RAL 7042)
-------	-----------------

# VIP-2/SC/FLK50 - Passive module

2900463

<https://www.phoenixcontact.com/us/products/2900463>



Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

## Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

## VIP-2/SC/FLK50 - Passive module


2900463

<https://www.phoenixcontact.com/us/products/2900463>



## Drawings

## Circuit diagram



# VIP-2/SC/FLK50 - Passive module

2900463

<https://www.phoenixcontact.com/us/products/2900463>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900463>

<b>cUL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	125 V	1 A	30 - 12	-

<b>UL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	125 V	1 A	30 - 12	-

# VIP-2/SC/FLK50 - Passive module

2900463

<https://www.phoenixcontact.com/us/products/2900463>



## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VIP-2/SC/FLK50 - Passive module

2900463

<https://www.phoenixcontact.com/us/products/2900463>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)