

# VIP-PT/FLK16/DS/FU/LED/AN/DV - Passive module

2903599

<https://www.phoenixcontact.com/us/products/2903599>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE interface module for 8 channels



## Your advantages

- These system-specific interface modules for DeltaV modules are used in combination with the relevant system cables
- Knife disconnect for each channel
- Pluggable fuse for each channel

## Commercial data

Item number	2903599
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C423
Product key	DK212K
GTIN	4046356948135
Weight per piece (including packing)	231.2 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85366990
Country of origin	US

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	16

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	63 mA (in as supplied state, with one 63 mA fuse)

### Supported controller EMERSON DeltaV

Suitable I/O card	VE4003S2B4
	VE4005S2B3
	VE4003S2B5
	SE4003S2B4

### Connection data

#### Field level

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14

#### Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	16
Pitch	2.54 mm

### Signaling

Status display present	yes, if the fuse fails
------------------------	------------------------

### Dimensions

#### Item dimensions

Width	57.1 mm
Height	110.8 mm
Depth	62.9 mm

### Material specifications

Color	gray (RAL 7042)
-------	-----------------

### Environmental and real-life conditions

# VIP-PT/FLK16/DS/FU/LED/AN/DV - Passive module

2903599

<https://www.phoenixcontact.com/us/products/2903599>



## Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--


# VIP-PT/FLK16/DS/FU/LED/AN/DV - Passive module

2903599

<https://www.phoenixcontact.com/us/products/2903599>



## Drawings



Connection scheme VIP-PT/FLK16/DS/FU/LED/AN/DV

## Classifications

### ECLASS

ECLASS-13.0	27141152
-------------	----------

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)