

UC-EMLP (27X18) CUS - Plastic label

0826970

<https://www.phoenixcontact.com/us/products/0826970>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 8, text field height: 18 mm, text field width: 27 mm



Your advantages

- All UC-EMLP ... self-adhesive device markers can also be supplied labeled according to customer requirements

Commercial data

Item number	0826970
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8147
GTIN	4046356448024
Weight per piece (including packing)	10.74 g
Weight per piece (excluding packing)	9.2 g
Country of origin	PL

UC-EMLP (27X18) CUS - Plastic label

0826970

<https://www.phoenixcontact.com/us/products/0826970>



Technical data

Product properties

Product type	Gerätemarker
Marking	
Number of individual labels	8
Number of individual labels per row	2
Identification technology	UV LED technology

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	1 Year

Mounting

Mounting type	adhesive

Material specifications

Adhesive strength	250 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	1 Year

Dimensions

Width	27.00 mm
Height	17.60 mm
Depth	1.00 mm

UC-EMLP (27X18) CUS - Plastic label

0826970

<https://www.phoenixcontact.com/us/products/0826970>



Length

18 mm

Standards and regulations

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

Standards

Standards/regulations

EN 45545-2

UC-EMLP (27X18) CUS - Plastic label

0826970

<https://www.phoenixcontact.com/us/products/0826970>



Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-EMLP (27X18) CUS - Plastic label

0826970

<https://www.phoenixcontact.com/us/products/0826970>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.109 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com