

# US-EMLP (85,6X54) YE CUS - Plastic label



0830119

<https://www.phoenixcontact.com/us/products/0830119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Card, can be ordered: by card, yellow, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 2, text field height: 54 mm, text field width: 85.6 mm



## Your advantages

- PVC material flammability rating V0 in accordance with UL 94

## Commercial data

Item number	0830119
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356614818
Weight per piece (including packing)	17.16 g
Weight per piece (excluding packing)	17.16 g
Country of origin	PL

0830119

<https://www.phoenixcontact.com/us/products/0830119>

## Technical data

### Product properties

Product type	Gerätemarker
--------------	--------------

### Marking

Number of individual labels	2
Number of individual labels per row	1
Identification technology	Thermal transfer for sheets and cards

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

### Mounting

Mounting type	adhesive
---------------	----------

### Material specifications

RoHS compliant	yes
Foil strength	500 µm
Adhesive strength	50 µm
Adhesive	Acrylic
Color	yellow (RAL 1018)
Material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

### Dimensions

Width	84.90 mm
Height	53.70 mm
Depth	0.55 mm

# US-EMLP (85,6X54) YE CUS - Plastic label



0830119

<https://www.phoenixcontact.com/us/products/0830119>

Length	53.7 mm
--------	---------

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# US-EMLP (85,6X54) YE CUS - Plastic label



0830119

<https://www.phoenixcontact.com/us/products/0830119>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 9.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# US-EMLP (85,6X54) YE CUS - Plastic label



0830119

<https://www.phoenixcontact.com/us/products/0830119>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)