

WML 14 (25X19)A4 - Cable marker label

0830693

<https://www.phoenixcontact.com/us/products/0830693>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker label, Sheet, white, unmarked, can be labeled with: Office printing systems, CMS-P1-PLOTTER, PLOTMARK, cable diameter range: 6.1 ... 14.2 mm, mounting type: adhesive, cable diameter: ≤ 14.2 mm, Number of individual labels: 28, text field height: 19.1 mm, text field width: 25 mm



Your advantages

- For indoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- For cylindrical objects, single wires, and cables

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0830693 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG12 |
| Product key | BG2314 |
| GTIN | 4046356718783 |
| Weight per piece (including packing) | 15.43 g |
| Weight per piece (excluding packing) | 15 g |
| Customs tariff number | 39199080 |
| Country of origin | DE |

WML 14 (25X19)A4 - Cable marker label

0830693

<https://www.phoenixcontact.com/us/products/0830693>



Technical data

Notes

| | |
|---------|---|
| General | Print image may vary depending on laser printer |
|---------|---|

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-------------------------------------|-----------------------|
| Number of individual labels | 28 |
| Number of individual labels per row | 7 |
| Identification technology | Office laser printing |

Dimensions

| | |
|--------|---------|
| Width | 25 mm |
| Height | 63.5 mm |
| Depth | 0.1 mm |

Material specifications

| | |
|----------------|-------------------------------|
| RoHS compliant | yes |
| Adhesive | Acrylic |
| Color | white (RAL 9010) |
| Material | Polyester |
| Components | Free from halogen and cadmium |

Cable/line

| | |
|-------------------------|--------------------|
| External cable diameter | ≤ 14.20 mm |
| | 6.1 mm ... 14.2 mm |

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

UV resistance

| | |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

| | |
|--------------------------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl [CAS No. 67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |

WML 14 (25X19)A4 - Cable marker label

0830693

<https://www.phoenixcontact.com/us/products/0830693>



| | |
|---|-------------|
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
|---|-------------|

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result | Test passed |
| Climate level | AHT 1.0 S |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result | Test passed |

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Ambient temperature (storage/transport) | 23 °C |
| Permissible humidity (storage/transport) | 50 % |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life | 2 years |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

WML 14 (25X19)A4 - Cable marker label

0830693

<https://www.phoenixcontact.com/us/products/0830693>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

WML 14 (25X19)A4 - Cable marker label

0830693

<https://www.phoenixcontact.com/us/products/0830693>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com