

UCT-EMP (60X15) CUS - Snap-in markers



1014123

<https://www.phoenixcontact.com/us/products/1014123>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 3, text field height: 15 mm, text field width: 60 mm



Your advantages

- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications
- The format automatically ensures printing with a high degree of positioning accuracy
- The wide temperature range means that the labels can be used in control cabinets as well as the field

Commercial data

Item number	1014123
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8138
GTIN	4046356783040
Weight per piece (including packing)	12.7 g
Weight per piece (excluding packing)	9.21 g
Country of origin	PL

UCT-EMP (60X15) CUS - Snap-in markers



1014123

<https://www.phoenixcontact.com/us/products/1014123>

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	3
Number of individual labels per row	1

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

Material specifications

Color	white (RAL 9010)
Material	PC
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Dimensions

Width	59.90 mm
Height	15.00 mm
Depth	0.95 mm
Length	15 mm

Standards and regulations

UCT-EMP (60X15) CUS - Snap-in markers



1014123

<https://www.phoenixcontact.com/us/products/1014123>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Standards	
Standards/regulations	EN 45545-2

UCT-EMP (60X15) CUS - Snap-in markers



1014123

<https://www.phoenixcontact.com/us/products/1014123>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

UCT-EMP (60X15) CUS - Snap-in markers



1014123

<https://www.phoenixcontact.com/us/products/1014123>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.038 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com