

SACB-8/16-L-C QO - Distributor box

1156006

<https://www.phoenixcontact.com/us/products/1156006>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, connection method: QUICKON, 0.14 mm² ... 0.5 mm², number of slots: 8, number of positions: 5, slot assignment: Double, status display: yes, PNP; master cable connection: Pluggable screw connection 180°, shielding: no, When connecting 5 conductors, max. 0.5 mm² can be connected

Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Convenient: increased machine availability thanks to quick and easy diagnostics
- Innovative and time-saving assembly with insulation displacement connection
- Flexible: distributor box with connector hood for on-site assembly

Commercial data

Item number	1156006
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF41
Product key	AF3DBD
GTIN	4063151157869
Weight per piece (including packing)	399.5 g
Weight per piece (excluding packing)	399.5 g
Customs tariff number	85366990
Country of origin	DE

SACB-8/16-L-C QO - Distributor box

1156006

<https://www.phoenixcontact.com/us/products/1156006>



Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".
Note on application	Cables with 5 conductors may have a maximum connection cross-section of 0.5 mm ² /20 AWG.

Product properties

Product type	Distributor box
Number of positions	5
Number of slots	8
LED	yes

System properties

Local diagnostics	
Monitored function	Supply voltage per module
Optical representation	Green LED

Electrical properties

Max. operating voltage U _{max}	30 V DC
Local diagnostics	Supply voltage per module Green LED
	Status display I/O Yellow LED
Nominal voltage U _N	24 V DC
Rated current, total	10 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

Connection data

Conductor connection	
Sensor/actuator connection system	QUICKON
Conductor cross section Flexible signal line	0.14 mm ² ... 0.5 mm ²
Conductor cross section Flexible power supply	0.14 mm ² ... 0.5 mm ²
Connection cross section AWG Flexible signal line	26 ... 20
Connection cross section AWG Flexible power supply	26 ... 20
Stripping length Signal line	7 mm
Stripping length of the sheath	50 mm (Master cable)
Tightening torque, cover screw	0.35 Nm
Tightening torque of mounting screw for fixing the housing	0.5 Nm
Tightening torque, union nut	4 Nm

SACB-8/16-L-C QO - Distributor box

1156006

<https://www.phoenixcontact.com/us/products/1156006>



Connection assignment

Slot/position = Wire color or connection

1 / 4 (A) = 1 / 4

1 / 2 (B) = 1 / 2

2 / 4 (A) = 2 / 4

2 / 2 (B) = 2 / 2

3 / 4 (A) = 3 / 4

3 / 2 (B) = 3 / 2

4 / 4 (A) = 4 / 4

4 / 2 (B) = 4 / 2

5 / 4 (A) = 5 / 4

5 / 2 (B) = 5 / 2

6 / 4 (A) = 6 / 4

6 / 2 (B) = 6 / 2

7 / 4 (A) = 7 / 4

7 / 2 (B) = 7 / 2

8 / 4 (A) = 8 / 4

8 / 2 (B) = 8 / 2

1-8 / 1 (+ 24 V) = U_N

1-8 / 3 (0 V) = 0 V

1-8 / 5 (PE) = PE


Signaling

Status display present

yes

Dimensions

Dimensional drawing



Width

58 mm

Height

45 mm

Length

168 mm

Wrench size, union nut

16 mm

Material specifications

Material Housing

PBT

Material Molding compound

PUR

Flammability rating according to UL 94

V0

Seal material O-ring

FKM

Seal material

FKM

SACB-8/16-L-C QO - Distributor box

1156006

<https://www.phoenixcontact.com/us/products/1156006>



Contact material	Steel/copper
Contact surface material	Sn
Contact carrier material	PA 6.6
Material of contact, master cable side	CU alloy
Material of the contact carrier on the master cable side	PA 6.6 V0
Material of contact surface, master cable side	Ni
Wire insulation material	PVC / PE / PP / rubber

Cable/line

External cable diameter	7 mm ... 12 mm
Connection method	Pluggable screw connection

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-30 °C ... 80 °C
	-5 °C ... 50 °C (During assembly)

SACB-8/16-L-C QO - Distributor box


1156006

<https://www.phoenixcontact.com/us/products/1156006>



Drawings

Dimensional drawing




SACB-8/16-L-C QO - Distributor box

1156006


<https://www.phoenixcontact.com/us/products/1156006>



Functional drawing



Schematic diagram



QUICKON connection, 5-pos.


SACB-8/16-L-C QO - Distributor box

1156006

<https://www.phoenixcontact.com/us/products/1156006>



Circuit diagram



SACB-8/16-L-C QO - Distributor box

1156006

<https://www.phoenixcontact.com/us/products/1156006>



Classifications

ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

ETIM

ETIM 9.0	EC003558
----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SACB-8/16-L-C QO - Distributor box

1156006

<https://www.phoenixcontact.com/us/products/1156006>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: n/a)
SCIP	4848ae31-8a78-47f3-bad8-ffbb2422101f

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com