

SP 4/ 1-M BU - Plug

3042793

<https://www.phoenixcontact.com/us/products/3042793>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 800 V, nominal current: 32 A, number of positions: 1, connection method: Spring-cage connection, Rated cross section: 4 mm², cross section: 0.08 mm²- 6 mm², color: blue

Product description

Connector element center, left housing with engagement pin, right opened without cover

Your advantages

- Cable housing can be snapped on to the plugs, see figure below
- The plug with spring-cage connection is assembled directly on site by snapping together single-position plug elements
- The ST-COMBI plugs for self-assembly provide solutions that users can implement themselves
- Tested for railway applications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3042793 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE02 |
| Product key | BE2144 |
| GTIN | 4017918956097 |
| Weight per piece (including packing) | 4.48 g |
| Weight per piece (excluding packing) | 4.48 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

Technical data

Notes

| | |
|--------------------|---|
| Notes on operation | COMBI connectors are connectors without switching power in accordance with IEC 61984 and can be connected or disconnected without load or voltage when used as intended |
| General | |
| Note | With a free-hanging connection, an insulating foil has to be placed between the plug connection and electrically conductive surfaces. |

Product properties

| | |
|---------------------|---------------|
| Product type | Terminal plug |
| Number of positions | 1 |
| Pitch | 6.2 mm |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---------------------|------|
| Rated surge voltage | 8 kV |
|---------------------|------|

Connection data

| | |
|---|---|
| Nominal cross section | 4 mm ² |
| Connection method | Spring-cage connection |
| Stripping length | 8 mm ... 10 mm |
| Internal cylindrical gage | A4 |
| Connection in acc. with standard | IEC 61984 |
| Conductor cross-section rigid | 0.08 mm ² ... 6 mm ² |
| Cross section AWG | 28 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.08 mm ² ... 4 mm ² |
| Conductor cross-section, flexible [AWG] | 28 ... 12 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 1 mm ² |
| Nominal current | 32 A |
| Maximum load current | 32 A (with 6 mm ² conductor cross-section) |
| Nominal voltage | 800 V |
| Nominal cross section | 4 mm ² |

Dimensions

| | |
|--------|--------|
| Width | 6.2 mm |
| Height | 21 mm |

SP 4/ 1-M BU - Plug

3042793

<https://www.phoenixcontact.com/us/products/3042793>



| | |
|--------|---------|
| Depth | 41.5 mm |
| Length | 21 mm |
| Pitch | 6.2 mm |

Material specifications

| | |
|--|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |

Electrical tests

Surge voltage test

| | |
|--|-------------|
| Result | Test passed |
| Short-time withstand current 4 mm ² | 0.48 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 2 kV |
| Result | Test passed |

Mechanical tests

Attachment on the carrier

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Environmental and real-life conditions

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 30 s |
| Result | Test passed |

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2018-05 |
| Spectrum | Long life test category 1, class B, body mounted |
| Frequency | f ₁ = 5 Hz to f ₂ = 150 Hz |
| ASD level | 0.964 (m/s ²) ² /Hz |
| Acceleration | 0.58g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-----------|
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |

SP 4/ 1-M BU - Plug



3042793

<https://www.phoenixcontact.com/us/products/3042793>

| | |
|-----------------|-----------------------------------|
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C (max. operating temperature see derating curve) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

SP 4/ 1-M BU - Plug


3042793

<https://www.phoenixcontact.com/us/products/3042793>




Drawings

Schematic diagram




Diagram



Derating curve for spring-cage terminals ST 4/1P.. and ST 4/2P.. with all plug versions SP 4/... . The derating curves are determined by multiplying the values of the base curves by the factor 0.8.

Diagram



Derating curve for the spring-cage terminal with all plug versions SP 4/...


SP 4/ 1-M BU - Plug

3042793

<https://www.phoenixcontact.com/us/products/3042793>



Diagram



Derating curve for ST 4/ 1P and for all plug versions SP... .

Circuit diagram



SP 4/ 1-M BU - Plug



3042793

<https://www.phoenixcontact.com/us/products/3042793>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3042793>

| | | CSA | | |
|---|--|-----------------------|-----------------------|-------------------|
| | | Approval ID: 13631 | | |
| | | Nominal voltage U_N | Nominal current I_N | Cross section AWG |
| B | | 600 V | 30 A | 24 - 12 |
| C | | 600 V | 30 A | 24 - 12 |

| | | IECEE CB Scheme | | |
|--|--|------------------------------|--|--|
| | | Approval ID: DE1-62736/B1/B2 | | |

| | | cULus Recognized | | |
|---|--|-----------------------|-----------------------|-------------------|
| | | Approval ID: E60425 | | |
| | | Nominal voltage U_N | Nominal current I_N | Cross section AWG |
| B | | 600 V | 30 A | 28 - 10 |
| C | | 600 V | 30 A | 28 - 10 |

| | | VDE Zeichengenehmigung | | |
|--------------------------|--|------------------------|-----------------------|-------------------|
| | | Approval ID: 40019518 | | |
| | | Nominal voltage U_N | Nominal current I_N | Cross section AWG |
| keine | | | | |
| Only flexible conductors | | 800 V | - | - |
| Only rigid conductors | | 800 V | - | - |
| | | | | 0.2 - 4 |
| | | | | 0.2 - 6 |

| | | EAC | | |
|--|--|---------------------------------|--|--|
| | | Approval ID: KZ7500651131219505 | | |

SP 4/ 1-M BU - Plug

3042793

<https://www.phoenixcontact.com/us/products/3042793>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250306 |
| ECLASS-15.0 | 27250306 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002021 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SP 4/ 1-M BU - Plug

3042793

<https://www.phoenixcontact.com/us/products/3042793>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com