

# CA-16P1N8A8007 - Cable connector

1619703

<https://www.phoenixcontact.com/us/products/1619703>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 6 mm ... 10 mm, coding: N, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1619703                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AB31                           |
| Product key                          | ABRAEA                         |
| GTIN                                 | 4046356822121                  |
| Weight per piece (including packing) | 90.8 g                         |
| Weight per piece (excluding packing) | 84.97 g                        |
| Customs tariff number                | 85366990                       |
| Country of origin                    | DE                             |

# CA-16P1N8A8007 - Cable connector

1619703

<https://www.phoenixcontact.com/us/products/1619703>



## Technical data

### Notes

|                    |  |
|--------------------|--|
| Order information: | Order 6 x Ø 1 mm crimp contacts separately |
|--------------------|--|

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Insulating body

|  |   |
|--|---|
| Note   | Order information: Order crimp contacts Ø 1 mm separately |
| Coding   | N   |
| Material (Insulating body)                             | PA 6.6  |
| Connection method                                      | Crimp connection  |
| Contact switching type                                 | Pin   |
| Application  | Signal  |
| Number of positions                                    | 16  |
| Direction of rotation                                  | Standard  |
| Connection profile                                     | 16  |
| Number Contact (Signal contacts)                       | 16  |
| Diameter Contact (Signal contacts)                     | 1 mm  |
| Litz wire cross-section min. Contact (Signal contacts) | 0.08 mm <sup>2</sup>                                      |
| Litz wire cross-section max. Contact (Signal contacts) | 1 mm <sup>2</sup>   |
| Rated current Contact (Signal contacts)                | 8 A (for max. connection cross section)                   |
| Rated voltage Contact (Signal contacts)                | 48 V AC   |
|  | 74 V DC   |
| Rated surge voltage                                    | 1.5 kV  |
| Overvoltage category                                   | III   |
| Degree of pollution                                    | 3   |

#### Housing

|                                   |  |
|-----------------------------------|--|
| Type                              | Cable connector housing  |
| Thread type                       | M23  |
| Design                            | straight   |
| Type of locking                   | Screw locking mechanism  |
| Pg screw connection               | none   |
| Housing material                  | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Material for screw connection     | CuZn   |
| Degree of protection (plugged in) | IP67   |

#### Seal

|                         |                |
|-------------------------|----------------|
| External cable diameter | 6 mm ... 10 mm |
| Seal material           | NBR            |

# CA-16P1N8A8007 - Cable connector

1619703

<https://www.phoenixcontact.com/us/products/1619703>



## Environmental and real-life conditions

### Ambient conditions

|  |                   |
|--|-------------------|
| Ambient temperature (operation)          | -40 °C ... 125 °C |
| Permissible humidity (storage/transport) | 50 % ... 65 %     |

# CA-16P1N8A8007 - Cable connector

1619703

<https://www.phoenixcontact.com/us/products/1619703>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619703>

| <b>cUL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  | 48 V                  | 3 A                   | 20                | -                    |

| <b>UL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                      |
|---|-----------------------|-----------------------|-------------------|----------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine   | 48 V                  | 5 A                   | 20                | -                    |

# CA-16P1N8A8007 - Cable connector

1619703

<https://www.phoenixcontact.com/us/products/1619703>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-16P1N8A8007 - Cable connector

1619703

<https://www.phoenixcontact.com/us/products/1619703>



## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|   |         |
|---|---------|
| Environment friendly use period (EFUP)  | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |         |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: n/a)                       |
| SCIP                                | bb47840b-e7a0-4788-bcfa-5a5066d5e5bb |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)