

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/us/products/5146147>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer for material off the roll, incl. Euro/US power cable, USB cable, and perforation knife. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English.

Product description

The THERMOMARK W2 has been specially developed for the double-sided printing and perforation of continuous shrink sleeves and continuous marking sleeves. You can easily create high-quality printed markers.

Your advantages

- The THERMOMARK W2 is an industrial printer with two 300 dpi print heads for double-sided printing of large quantities of shrink sleeves in roll/continuous format
- The guide elements ensure easy handling when inserting the sleeve
- Double-sided printing ensures optimum marking legibility
- Thanks to the perforation cutter, the shrink or marking sleeve can be quickly and easily perforated in the desired lengths. The connected markers are easily separated along the perforations
- Maintenance-free operation with proven thermal transfer printer technology
- Easy to control with the PROJECT COMPLETE software
- USB and Ethernet connections

Commercial data

Item number	5146147
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
GTIN	4046356327329
Weight per piece (including packing)	17,000 g
Weight per piece (excluding packing)	17,000 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/us/products/5146147>



Technical data

Product properties

Product type	Marking system
Marking	
Identification technology	Thermotransfer
Device properties	
Print width	105.6 mm
Print resolution	300 dpi
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

Electrical properties

Supply	
Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)

Dimensions

Width	780 mm
Height	405 mm
Length	554 mm

Material specifications

Color	gray
-------	------

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	10 °C ... 35 °C

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/us/products/5146147>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5146147>



EAC

Approval ID: RU D-DE.GB09.B.00141



EAC-RoHS

Approval ID: RU D-DE.HB49.B.00023

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/us/products/5146147>



Classifications

ECLASS

ECCLASS-13.0	19140104
--------------	----------

ETIM

ETIM 9.0	EC001684
----------	----------

UNSPSC

UNSPSC 21.0	43212100
-------------	----------

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/us/products/5146147>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com