

THERMOMARK GO - Thermal transfer printer

1090747

<https://www.phoenixcontact.com/us/products/1090747>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mobile thermal transfer printer for marking materials in cartridge format incl. accessories. The printer can print prepunched labels as well as materials in continuous format up to a material width of 24 mm

Product description

The THERMOMARK GO is a mobile printer that elevates the digitalization of industrial identification to a new level with its intuitive operation via smart device. Controlled via the MARKING system app, the robust printer creates markings directly on site. Features such as state-of-the-art interfaces, fully guided creation of application-specific identification solutions, and automatic material detection make the process of creating markings particularly easy and error-free. The ability to print die-cut materials as well as continuous media offers professional users a wide variety of applications in industry and trade.

Note:

This product is approved for the following countries only and may only be used in these countries.

Andorra, Armenia, Australia, Austria, Belgium, Brazil, Bulgaria, Canada, Chile, China, Croatia, Cyprus, Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, Ireland, Italy, Japan, Kazakhstan, Kyrgyzstan, Latvia, Liechtenstein, Lithuania, Luxembourg, Malta, Mexico, Monaco, Morocco, Netherlands, New Zealand, Norway, Poland, Portugal, Romania, San Marino, Singapore, Slovakia, Slovenia, Spain, Sweden, Switzerland, Turkey, Ukraine, United Kingdom, USA, Vatican City

Scope of supply:

THERMOMARK GO, battery, power supply unit incl. 4 adapters, USB cable, MM-EML (20X8)R C1 WH/BK, brief instructions

Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- Operated entirely via digital devices using the MARKING system app
- User-friendly operation with context-based menu navigation of the MARKING system app and Application Wizards for easily creating application-specific marking solutions
- The THERMOMARK GO prints materials in cartridge format, which contain the material to be marked and the appropriate ink ribbon
- Easy material change with the uniform GO SERIES cartridge system
- Alternative control via the PROJECT complete software

Commercial data

Item number	1090747
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
GTIN	4055626901510

THERMOMARK GO - Thermal transfer printer

1090747

<https://www.phoenixcontact.com/us/products/1090747>



Weight per piece (including packing)	1,812.17 g
Weight per piece (excluding packing)	1,174 g
Customs tariff number	84433210
Country of origin	CN

THERMOMARK GO - Thermal transfer printer

1090747

<https://www.phoenixcontact.com/us/products/1090747>



Technical data

Product properties

Product type	Marking system
Scope of supply	THERMOMARK GO, battery, power supply unit incl. 4 adapters, USB cable, MM-EML (20X8)R C1 WH/BK, brief instructions

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Device properties

Print width	22 mm
Print resolution	203 dpi
Operating system	Windows 10, Windows Server 2016, Windows Server 2019, Windows Server 2022

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	135 mm
Height	175 mm
Length	70 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C
---------------------------------	----------------

THERMOMARK GO - Thermal transfer printer

1090747

<https://www.phoenixcontact.com/us/products/1090747>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1090747>



EAC

Approval ID: RU D-DE.GB09.B.00141



EAC

Approval ID: RU0000049188



EAC-RoHS

Approval ID: RU D-DE.HB49.B.00023



cULus Listed

Approval ID: E140403



FCC

Approval ID: SQBL652

Industry Canada

Approval ID: 3147A-BL652

ANATEL

Approval ID: 13250-21-06497



CCC

Approval ID: 2021010904441897

EU-Type Examination Certificate

Approval ID: UL TEC-03687

EU-Type Examination Certificate

Approval ID: 0370-RED-4490

THERMOMARK GO - Thermal transfer printer

1090747

<https://www.phoenixcontact.com/us/products/1090747>



Classifications

ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

ETIM

ETIM 9.0	EC001684
----------	----------

UNSPSC

UNSPSC 21.0	43212100
-------------	----------

THERMOMARK GO - Thermal transfer printer

1090747

<https://www.phoenixcontact.com/us/products/1090747>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com