

MM-EML (EX18)R C1 TR/BK - Label



1116130

<https://www.phoenixcontact.com/us/products/1116130>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, transparent/black, unmarked, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, roll length: 8 m, text field height: 16 mm, text field width: 8000 mm

Product description

The MM-EML... polyester self-adhesive labels are available as continuous media for equipment marking.

Your advantages

- The material is cUL certified
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application

Commercial data

Item number	1116130
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG241E
GTIN	4063151041151
Weight per piece (including packing)	69.9 g
Weight per piece (excluding packing)	58 g
Customs tariff number	96121010
Country of origin	CN

MM-EML (EX18)R C1 TR/BK - Label

1116130

<https://www.phoenixcontact.com/us/products/1116130>



Technical data

Product properties

Product type	Gerätemarker
Marking	
Identification technology	Thermal transfer

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Foil strength	25 µm
Adhesive	Acrylic
Color	multicolored transparent black (RAL 9005)
Material	Polyester
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months

Dimensions

Length of roll	8.00 m
Height	18 mm
Depth	0.06 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

MM-EML (EX18)R C1 TR/BK - Label

1116130

<https://www.phoenixcontact.com/us/products/1116130>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1116130>



cULus Recognized

Approval ID: MH48542

MM-EML (EX18)R C1 TR/BK - Label

1116130

<https://www.phoenixcontact.com/us/products/1116130>



Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

MM-EML (EX18)R C1 TR/BK - Label

1116130

<https://www.phoenixcontact.com/us/products/1116130>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com