

CUC-SP-J1ST-A/R4LT-LED - RJ45 PCB connector



1149867

<https://www.phoenixcontact.com/us/products/1149867>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 PCB connector, number of positions: 8, 10 Gbps, Wave soldering, degree of protection: IP20, connection method: THT wave, Tray

Your advantages

- The right version for every application. Available with and without LED, single- and multi-port
- The extended temperature range from -40 °C to +85 °C enables use in demanding applications
- Through-hole technology (THT) provides high mechanical stability when connecting the female connector to the PCB

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1149867 |
| Packing unit | 80 pc |
| Minimum order quantity | 80 pc |
| Sales key | AB12 |
| Product key | ABNADA |
| GTIN | 4063151145866 |
| Weight per piece (including packing) | 4.95 g |
| Weight per piece (excluding packing) | 4.5 g |
| Customs tariff number | 85366930 |
| Country of origin | TW |

CUC-SP-J1ST-A/R4LT-LED - RJ45 PCB connector



1149867

<https://www.phoenixcontact.com/us/products/1149867>

Technical data

Product properties

| | |
|------------------------|------------------------------|
| Product type | Data connector (device side) |
| Number of positions | 8 |
| Connection profile | RJ45 |
| Housing shield springs | No |
| Number of slots | 1 |
| Shielded | yes |
| LED | yes |

Insulation characteristics

| | |
|----------------------|---|
| Overvoltage category | I |
| Degree of pollution | 2 |

Electrical properties

| | |
|-----------------------------|------------------|
| Rated voltage (III/2) | 72 V DC |
| Rated surge voltage | 1.5 kV DC |
| Rated surge voltage (III/3) | 1.5 kV |
| Rated surge voltage | 1 kV DC |
| Rated current | 1.5 A |
| Frequency range | 10 Hz ... 500 Hz |
| Insulation resistance | > 500 MΩ |
| Test voltage | 1 kV DC |
| Test voltage Core/Core | 1 kV DC |
| Test voltage Core/Shield | 1.50 kV DC |
| Transmission medium | Copper |
| Transmission speed | 10 Gbps |
| Transmission speed | 10 Gbps |
| Power transmission | PoE++ |

Connection data

| | |
|-----------------------|----------|
| Connection technology | |
| Connection method | THT wave |

Dimensions

| | |
|--------------------|----------|
| Width | 16.18 mm |
| Height | 11.3 mm |
| Length | 15 mm |
| Installed height | 11.30 mm |
| Orientation to PCB | 90.00 ° |
| Data pin length | 2.40 mm |

Material specifications

CUC-SP-J1ST-A/R4LT-LED - RJ45 PCB connector



1149867

<https://www.phoenixcontact.com/us/products/1149867>

| | |
|--|------------------------------------|
| Material Metal surface contact area (top layer) | Au (0.152 µm/6 µ") |
| Material Metal surface contact area (middle layer) | Ni (1.27 µm/50 µ") |
| Material Metal surface soldering area (middle layer) | Ni (1.27 µm/50 µ") |
| Material | Copper alloy (Housing (shielding)) |
| Material Contact | Phosphor bronze |
| Material Contact carrier | PA 9T GF |
| Material Housing | Metal |
| Flammability rating according to UL 94 | V0 |

Cable/line

| | |
|--------------------------|------------|
| Test voltage Core/Core | 1 kV DC |
| Test voltage Core/Shield | 1.50 kV DC |
| Halogen-free | no |
| Flame resistance | UL 94 V0 |

Mechanical properties

| | |
|-------------------------------------|-----------|
| Mechanical data | |
| Insertion/withdrawal cycles | > 750 |
| Insertion force per signal contact | < 20.00 N |
| Extraction force per signal contact | < 20 N |

Environmental and real-life conditions

| | |
|--------------------|------------------------|
| Test specification | |
| Frequency | 10-500 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.35 mm |
| Acceleration | 50.00 m/s ² |
| Test duration | 20.00 s |

| | |
|--------------------|-------------------------|
| Test specification | |
| Specification | IEC60068-2-27 |
| Acceleration | 295.00 m/s ² |

| | |
|---|------------------|
| Ambient conditions | |
| Degree of protection (when plugged in) | IP20 |
| Degree of protection (not plugged in) | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

Standards and regulations

| | |
|------------------|----------|
| Flame resistance | UL 94 V0 |
|------------------|----------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Wave soldering |
|---------------|----------------|

CUC-SP-J1ST-A/R4LT-LED - RJ45 PCB connector

1149867

<https://www.phoenixcontact.com/us/products/1149867>



Processing notes

Classification temperature T_c

260 °C


Packaging specifications

Type of packaging

Tray

Drawings

Diagram



Classification wave soldering profile

CUC-SP-J1ST-A/R4LT-LED - RJ45 PCB connector

1149867

<https://www.phoenixcontact.com/us/products/1149867>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1149867>



cUL Recognized

Approval ID: FILE E 335024



UL Recognized

Approval ID: FILE E 335024

CUC-SP-J1ST-A/R4LT-LED - RJ45 PCB connector

1149867

<https://www.phoenixcontact.com/us/products/1149867>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CUC-SP-J1ST-A/R4LT-LED - RJ45 PCB connector

1149867

<https://www.phoenixcontact.com/us/products/1149867>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com