

# NBC-USB3.0-UCM/3,0-PVC/UCM - USB cable



1333214

<https://www.phoenixcontact.com/us/products/1333214>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

USB cable, design: USB-C, degree of protection: IP20, cable length: 3 m, number of positions: 24, 5 Gbps, cable outlet: straight, USB 3.2 Gen. 1



## Your advantages

- High-speed data transmission up to 5 Gbps
- Minimal space requirements thanks to USB-C connectors
- Reliable data transmission thanks to 100 % testing

## Commercial data

Item number	1333214
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB14
Product key	ABNDBB
GTIN	4063151629786
Weight per piece (including packing)	152.2 g
Weight per piece (excluding packing)	152.2 g
Customs tariff number	85444290
Country of origin	CN

# NBC-USB3.0-UCM/3,0-PVC/UCM - USB cable



1333214

<https://www.phoenixcontact.com/us/products/1333214>

## Technical data

### Product properties

Product type	Data cable preassembled
Type	USB-C
Sensor type	USB 3.2 Gen. 1
Number of positions	24
Connection profile	USB-C
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Interfaces

Transmission speed	5 GBit/s
--------------------	----------

### Electrical properties

Rated voltage	20 V (Contacts)
Rated current	5 A
Insulation resistance	10 MΩ
Test voltage	300 V AC
	300 V AC
Test voltage Core/Core	300 V AC
Test voltage Core/Shield	300.00 V AC
Contact resistance	< 40 mΩ
Transmission speed	5 Gbps
Transmission characteristics (category)	USB 3.2 Gen 1
Transmission speed	5 GBit/s

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 8 N
Max. bending cycles	100
Smallest bending radius	3,7xD

### Material specifications

Color of the housing part	black
Outer sheath, material	PVC
Conductor material	Cu

# NBC-USB3.0-UCM/3,0-PVC/UCM - USB cable



1333214

<https://www.phoenixcontact.com/us/products/1333214>

## Dimensions

Width	12.3 mm
Height	8.8 mm
Length	40.65 mm

## Connector

### Connection 1

Type	Plug straight USB type C
Shielded	yes
Insertion/withdrawal cycles	10000
Insulation resistance	10 MΩ
Overtoltage category	I
Degree of pollution	2
Degree of protection	IP20

### Connection 2

Type	Plug straight USB type C
Shielded	yes
Insertion/withdrawal cycles	10000
Insulation resistance	10 MΩ
Degree of pollution	2
Degree of protection	IP20

## Cable/line

Cable length	3.00 m
--------------	--------

### PVC USB 3.0 black [USB]

Shielded	yes
Cable type	PVC USB 3.0 black
Cable type (abbreviation)	USB
External cable diameter	5.00 mm
Outer sheath, material	PVC
External sheath, color	black
Shielding	Aluminum-lined foil

## Environmental and real-life conditions

### Test specification

Cold stress	-40 °C/96 h
Thermal stress	85 °C/96 h
Corrosive stress	Salt spray test UL364-26
Insulation resistance, neighboring contacts	10 MΩ

### Ambient conditions

Degree of protection	IP20
----------------------	------

# NBC-USB3.0-UCM/3,0-PVC/UCM - USB cable



1333214

<https://www.phoenixcontact.com/us/products/1333214>

Ambient temperature (operation)	-25 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

# NBC-USB3.0-UCM/3,0-PVC/UCM - USB cable



1333214

<https://www.phoenixcontact.com/us/products/1333214>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060328

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# NBC-USB3.0-UCM/3,0-PVC/UCM - USB cable



1333214

<https://www.phoenixcontact.com/us/products/1333214>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)