

UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal strip marker carrier for identifying terminal groups, for installation on the NS 32 or NS 35/7.5 terminal strips, marking field size: 60 x 10 mm

Commercial data

Item number	0803719
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG12
Product key	BG211A
GTIN	4055626146263
Weight per piece (including packing)	9.8 g
Weight per piece (excluding packing)	8.035 g
Customs tariff number	39269097
Country of origin	CN

UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	280.70 mm
Height	62.60 mm
Depth	46.50 mm

Material specifications

RoHS compliant	yes
Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Base element material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

Standards and regulations

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	latching
---------------	----------

UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UBE/D (60X10) - Marker carriers



0803719
<https://www.phoenixcontact.com/us/products/0803719>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.068 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com