

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017237

<https://www.phoenixcontact.com/us/products/2017237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 800 V, nominal current: 32 A, 1st level connection left, connection method: Screw connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, connection method: Spade connection, mounting: NS 35/7,5, NS 35/15, NS 32, color: gray

## Your advantages

- Designation read from the front
- Terminal blocks and bridge connections eliminated
- Attractive appearance due to the elegant conductor conduit in the lateral cable ducts
- User-friendly operation, i.e., unobstructed view of plugs, good access to plugs, and fast connection check

## Commercial data

Item number	2017237
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE05
Product key	BE511X
GTIN	4017918052690
Weight per piece (including packing)	11.24 g
Weight per piece (excluding packing)	10.899 g
Customs tariff number	85369010
Country of origin	PL

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block

2017237

<https://www.phoenixcontact.com/us/products/2017237>



## Technical data

### Product properties

Product type	Feed-through terminal block
Product family	UHK
Number of connections	2
Number of rows	1
Potentials	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

### Connection data

Number of connections per level	2
Nominal cross section	4 mm <sup>2</sup>

### 1st level connection left

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	9 mm
Internal cylindrical gage	A3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Cross section AWG	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Cross-section with insertion bridge, rigid	4 mm <sup>2</sup>
Cross-section with insertion bridge, flexible	4 mm <sup>2</sup>
2 conductors with same cross section, solid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
2 conductors with same cross section, flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Nominal current	32 A
Maximum load current	40 A (with 4 mm <sup>2</sup> conductor cross-section)
Nominal voltage	800 V
Nominal cross section	4 mm <sup>2</sup>

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017237

<https://www.phoenixcontact.com/us/products/2017237>

Connection method	Spade connection
-------------------	------------------

## Dimensions

Width	6.2 mm
End cover width	2.3 mm
Height	54 mm
Depth on NS 32	56.5 mm
Depth on NS 35/7,5	51.5 mm
Depth on NS 35/15	59 mm

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

## Mechanical properties

Mechanical data	
Open side panel	Yes

## Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

## Mounting

NS 35/7,5

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block

2017237

<https://www.phoenixcontact.com/us/products/2017237>



Mounting type	NS 35/15
	NS 32

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block

2017237

<https://www.phoenixcontact.com/us/products/2017237>



## Drawings

Circuit diagram




# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017237

<https://www.phoenixcontact.com/us/products/2017237>

Circuit diagram



1 = cover

2 = fixed bridge

3 = insertion bridge

4 = isolator bridge bar

5 = bridge bar isolator

6 = separating plate

7 = partition plate

8 = test plug socket

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017237

<https://www.phoenixcontact.com/us/products/2017237>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2017237>

		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		600 V	20 A	28 - 14	-

		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
B		250 V	25 A	28 - 12	-
C		150 V	25 A	28 - 12	-

		EAC	Approval ID: RU C-DE.BL08.B.00541

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block

2017237

<https://www.phoenixcontact.com/us/products/2017237>



## Classifications

### ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

### ETIM

ETIM 9.0	EC000897
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UHK 4-FS(8-2,8-0,8) - Feed-through terminal block

2017237

<https://www.phoenixcontact.com/us/products/2017237>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)