

# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE, consisting of basic terminal block with screw connection and plug-in miniature relay with internal amplifier circuit and an appropriate auxiliary supply for weak signal sources, 1 N/O contact, 5 V DC nominal input voltage

## Commercial data

Item number	1094759
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	C461
Product key	DK6226
GTIN	4055626918891
Weight per piece (including packing)	36.17 g
Weight per piece (excluding packing)	32.12 g
Customs tariff number	85364190
Country of origin	DE

# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



## Technical data

### Product properties

Product type	Relay Module
Product family	PLC-INTERFACE
Application	weak signal sources
Operating mode	100% operating factor
Mechanical service life	$2 \times 10^7$ cycles

### Data management status

Date of last data management	12.09.2025
------------------------------	------------

### Electrical properties

Maximum power dissipation for nominal condition	0.22 W
Insulation characteristics: Coil/contact	
Rated insulation voltage	250 V
Rated impulse withstand voltage	6 kV
Overvoltage category	III
Degree of pollution	3

### Supply

Nominal supply voltage	24 V DC (Us)
Voltage range with reference to $U_S$	0.8 ... 1.2
Input current	9 mA

### Input data

Coil side	
Nominal input voltage $U_N$	5 V DC
Input voltage range	4.5 V DC ... 6 V DC (20 °C)
Nominal voltage (plugged-in electromechanical relay)	24 V DC
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at $U_N$	1 mA
Typical response time	5 ms
Typical release time	7 ms
Protective circuit	Reverse polarity protection
	Surge protection
Operating voltage display	Yellow LED

### Output data

Switching	
Contact switching type	1 N/O contact
Type of switch contact	Single contact

# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



Contact connection type	Power contact
Contact material	AgSnO
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	12 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	10 A (4 s)
Min. switching current	10 mA
Short-circuit current	200 A (conditional short-circuit current)
Interrupting rating (ohmic load) max.	140 W (at 24 V DC) 20 W (at 48 V DC) 18 W (at 60 V DC) 23 W (at 110 V DC) 40 W (at 220 V DC) 1500 VA (for 250 V AC)
Switching capacity min.	120 mW
Output fuse	4 A gL/gG NEOZED

## Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Single ferrule) 2x 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule)
Conductor cross-section AWG	26 ... 14
Tightening torque	0.45 Nm ... 0.55 Nm (Usually these terminal blocks must be supported during conductor connection (held by one hand, supported on the housing))

## Dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm

## Material specifications

Color	gray (RAL 7042)
-------	-----------------

## Environmental and real-life conditions

Ambient conditions	
Degree of protection (Relay base)	IP20 (Relay base)
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



Altitude

≤ 2000 m

## Approvals

CE

Certificate

CE-compliant

UKCA

Certificate

UKCA-compliant

Shipbuilding approval

Certificate

TAE0000196

Corrosive gas test

Identification

ISA-S71.04. G3 Harsh Group

EN 60068-2-60

Shipbuilding data

Temperature

D

Humidity

A

Vibration

B/C

EMC

B

Enclosure

Required protection according to the Rules shall be provided upon installation on board

## EMC data

Electromagnetic compatibility

Conformance with EMC directive

Low Voltage Directive

Conformance with Low Voltage Directive

## Standards and regulations

Standards/regulations

IEC 60947-5-1

## Mounting

Mounting type

DIN rail mounting

Assembly note

in rows with zero spacing

Mounting position

any

# PLC-RSC- 5DC/1/SSI - Relay module


1094759

<https://www.phoenixcontact.com/us/products/1094759>



## Drawings

Diagram



① 250 V AC, ohmic load

Electrical service life


# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



Diagram



Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^{\circ}\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^{\circ}\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^{\circ}\text{C}$ .

Circuit diagram



# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1094759>



**EAC**

Approval ID: RU\*C-DE.\*08.B.00010



**EAC**

Approval ID: RU D-DE.B\*00573/18



**cULus Listed**

Approval ID: E140324

# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

### ETIM

ETIM 9.0	EC001437
----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# PLC-RSC- 5DC/1/SSI - Relay module

1094759

<https://www.phoenixcontact.com/us/products/1094759>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e4c5f1dc-be58-47c8-a28d-10b5e07dceaf

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)