

CUC-MP-J1ST-A/2R4LT-LED - RJ45 PCB connector

1149854

<https://www.phoenixcontact.com/us/products/1149854>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

RJ45 PCB connector, number of positions: 8, 10 Gbps, Wave soldering, degree of protection: IP20, connection method: THT wave, Tray



Your advantages

- The right version for every application. Available with and without LED, single- and multi-port
- The extended temperature range from -40 °C to +85 °C enables use in demanding applications
- Through-hole technology (THT) provides high mechanical stability when connecting the female connector to the PCB

Commercial data

Item number	1149854
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB12
Product key	ABNADA
GTIN	4063151146214
Weight per piece (including packing)	10.66 g
Weight per piece (excluding packing)	10.66 g
Customs tariff number	85366930
Country of origin	TW

CUC-MP-J1ST-A/2R4LT-LED - RJ45 PCB connector



1149854

<https://www.phoenixcontact.com/us/products/1149854>

Technical data

Product properties

Product type	Data connector (device side)
Number of positions	8
Connection profile	RJ45
Housing shield springs	Yes
Number of slots	2
Shielded	yes
LED	yes

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage	72 V DC
Rated surge voltage	1.5 kV DC
Rated current	1.5 A
Frequency range	10 Hz ... 500 Hz
Insulation resistance	> 500 MΩ
Transmission speed	10 Gbps
Transmission speed	10 Gbps
Power transmission	PoE++

Connection data

Connection technology	
Connection method	THT wave

Dimensions

Width	32.26 mm
Height	13.3 mm
Length	15.75 mm
Installed height	13.68 mm
Orientation to PCB	90.00 °
Data pin length	2.54 mm

Material specifications

Material Metal surface contact area (top layer)	Au (0.152 µm/6 µ")
Material Metal surface contact area (middle layer)	Ni (1.27 µm/50 µ")
Material Metal surface soldering area (middle layer)	Ni (1.27 µm/50 µ")
Material Metal surface soldering area (top layer)	Sn (2.54 µm/100 µ")
Material	(Housing (shielding))
Material Contact	Phosphor bronze

CUC-MP-J1ST-A/2R4LT-LED - RJ45 PCB connector

1149854

<https://www.phoenixcontact.com/us/products/1149854>



Material Contact carrier	PA 9T GF
Material Housing	Metal

Cable/line

Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Halogen-free	no
Flame resistance	UL 94 V0

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 750
Insertion force	20 N
Withdrawal force	20 N

Environmental and real-life conditions

Test specification

Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s ²
Test duration	20.00 s

Test specification

Specification	IEC60068-2-27
Acceleration	295.00 m/s ²

Ambient conditions

Degree of protection (when plugged in)	IP20
Degree of protection (not plugged in)	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Standards and regulations

Flame resistance	UL 94 V0
------------------	----------

Mounting

Mounting type	Wave soldering
---------------	----------------

Processing notes


Classification temperature T _c	260 °C
---	--------

Packaging specifications

Type of packaging	Tray
-------------------	------

Drawings

Diagram



Classification wave soldering profile

CUC-MP-J1ST-A/2R4LT-LED - RJ45 PCB connector

1149854

<https://www.phoenixcontact.com/us/products/1149854>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1149854>



cUL Recognized

Approval ID: FILE E 335024



UL Recognized

Approval ID: FILE E 335024

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com