

# SP 2,5/ 2 NZ:4 - Plug



3061143

<https://www.phoenixcontact.com/us/products/3061143>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 500 V, nominal current: 24 A, number of positions: 2, connection method: Spring-cage connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.08 mm<sup>2</sup>- 4 mm<sup>2</sup>, color: gray

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3061143       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 1 pc          |
| Product key                          | BE2144        |
| GTIN                                 | 4046356160827 |
| Weight per piece (including packing) | 7.01 g        |
| Weight per piece (excluding packing) | 7.01 g        |
| Country of origin                    | PL            |

# SP 2,5/ 2 NZ:4 - Plug

3061143

<https://www.phoenixcontact.com/us/products/3061143>



## Technical data

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | Terminal plug |
| Number of positions | 2             |
| Pitch               | 5.2 mm        |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                     |      |
|---------------------|------|
| Rated surge voltage | 6 kV |
|---------------------|------|

### Connection data

|                                                                                           |                                                       |
|-------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Nominal cross section                                                                     | 2.5 mm <sup>2</sup>                                   |
| Connection method                                                                         | Spring-cage connection                                |
| Stripping length                                                                          | 10 mm                                                 |
| Internal cylindrical gage                                                                 | A3                                                    |
| Connection in acc. with standard                                                          | IEC 61984                                             |
| Conductor cross-section rigid                                                             | 0.08 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Cross section AWG                                                                         | 28 ... 12 (converted acc. to IEC)                     |
| Conductor cross-section flexible                                                          | 0.08 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>          |
| Conductor cross-section, flexible [AWG]                                                   | 28 ... 14 (converted acc. to IEC)                     |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>          |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>          |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup>                                   |
| Nominal current                                                                           | 24 A                                                  |
| Maximum load current                                                                      | 24 A (with 4 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage                                                                           | 500 V                                                 |
| Nominal cross section                                                                     | 2.5 mm <sup>2</sup>                                   |

### Dimensions

|        |         |
|--------|---------|
| Width  | 10.4 mm |
| Height | 39 mm   |
| Length | 15.8 mm |
| Pitch  | 5.2 mm  |

### Material specifications

|                                        |                 |
|----------------------------------------|-----------------|
| Color                                  | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0              |
| Insulating material group              | I               |
| Insulating material                    | PA              |

# SP 2,5/ 2 NZ:4 - Plug



3061143

<https://www.phoenixcontact.com/us/products/3061143>

|                                                                         |             |
|-------------------------------------------------------------------------|-------------|
| Static insulating material application in cold                          | -60 °C      |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C      |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C      |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg    |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed      |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed      |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed      |

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

## Standards and regulations

|                                  |           |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

# SP 2,5/ 2 NZ:4 - Plug

3061143

<https://www.phoenixcontact.com/us/products/3061143>



## Drawings

### Circuit diagram



# SP 2,5/ 2 NZ:4 - Plug

3061143

<https://www.phoenixcontact.com/us/products/3061143>



## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC002021 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SP 2,5/ 2 NZ:4 - Plug



3061143  
<https://www.phoenixcontact.com/us/products/3061143>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)