

# SAC-5P-10,0-924/FS SCO - Bus system cable



1405987

<https://www.phoenixcontact.com/us/products/1405987>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, CANopen®, DeviceNet™, 5-position, PVC, gray, shielded, free cable end, on Socket straight M12, coding: A, cable length: 10 m, Connector unshielded

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1405987                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF15                           |
| Product key                          | AF1IHE                         |
| GTIN                                 | 4046356800419                  |
| Weight per piece (including packing) | 619.1 g                        |
| Weight per piece (excluding packing) | 604 g                          |
| Customs tariff number                | 85444290                       |
| Country of origin                    | US                             |

# SAC-5P-10,0-924/FS SCO - Bus system cable



1405987

<https://www.phoenixcontact.com/us/products/1405987>

## Technical data

### Product properties

|                      |                         |
|----------------------|-------------------------|
| Product type         | Data cable preassembled |
| Application          | Standard, U.S. cables   |
| Sensor type          | CANopen®                |
| Number of positions  | 5                       |
| No. of cable outlets | 1                       |
| Shielded             | yes                     |
| Coding               | A                       |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Interfaces

|                      |                     |
|----------------------|---------------------|
| Bus system           | CANopen®/DeviceNet™ |
| Signal type/category | CANopen®            |
|                      | DeviceNet™          |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties

|                                |          |
|--------------------------------|----------|
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 48 V AC  |
|                                | 60 V DC  |
| Nominal current I <sub>N</sub> | 4 A      |
| Transmission medium            | Copper   |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Connector

#### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

# SAC-5P-10,0-924/FS SCO - Bus system cable



1405987

<https://www.phoenixcontact.com/us/products/1405987>

## Connection 2

|                     |                     |
|---------------------|---------------------|
| Type                | Socket straight M12 |
| Number of positions | 5                   |
| Coding type         | A (Standard)        |

## Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

## CANopen®/DeviceNet™, PVC, gray [924]

|                                     |                                                                                    |
|-------------------------------------|------------------------------------------------------------------------------------|
| Dimensional drawing                 |  |
| Cable weight                        | 64.51 kg/km                                                                        |
| UL AWM Style                        | 2464 (80°C/300 V)                                                                  |
| Number of positions                 | 4                                                                                  |
| Shielded                            | yes                                                                                |
| Cable type                          | CANopen®/DeviceNet™, PVC, gray [924]                                               |
| Conductor structure                 | 2xAWG22 (Signal) + 2xAWG22 (Power)                                                 |
| Signal runtime                      | 4.46 ns/m                                                                          |
| Conductor structure signal line     | 19x 0.15 mm                                                                        |
| AWG signal line                     | 22                                                                                 |
| Conductor structure, voltage supply | 19x 0.15 mm                                                                        |
| AWG power supply                    | 22                                                                                 |
| Conductor cross section             | 2x 0.34 mm² (Signal line)<br>2x 0.34 mm² (Power supply)                            |
| Wire diameter incl. insulation      | 1.27 mm ±0.05 mm (Signal line)<br>2.24 mm ±0.13 mm (Power supply)                  |
| External cable diameter             | 6.90 mm ±0.13 mm                                                                   |
| Outer sheath, material              | PVC                                                                                |
| External sheath, color              | gray                                                                               |
| Conductor material                  | Bare Cu litz wires                                                                 |
| Material wire insulation            | Foamed PE (Signal line)<br>PVC (Power supply)                                      |
| Single wire, color                  | red-black, blue-white                                                              |
| Twisted pairs                       | 2 cores to the pair                                                                |
| Type of pair shielding              | Plastic-coated aluminum foil, aluminum side inside                                 |
| Overall twist                       | 2 pairs around a drain wire in the center to the core                              |
| Insulation resistance               | ≥ 59.38 Ω*m (Signal line)<br>≥ 57.41 GΩ*km (Power supply)                          |

# SAC-5P-10,0-924/FS SCO - Bus system cable



1405987

<https://www.phoenixcontact.com/us/products/1405987>

|                                               |                                              |
|-----------------------------------------------|----------------------------------------------|
| Wave impedance                                | 120 $\Omega$ $\pm$ 12 $\Omega$               |
| Working capacitance                           | nom. 78.74 pF (per meter)                    |
| Minimum bending radius, flexible installation | 15 x D                                       |
| Smallest bending radius, movable installation | 104 mm                                       |
| Shield attenuation                            | 0.95 dB (f = 125 kHz)                        |
|                                               | 1.64 dB (f = 500 kHz)                        |
|                                               | 2.30 dB (f = 1 MHz)                          |
| Flame resistance                              | FT4                                          |
| Resistance to oil                             | yes                                          |
| Other resistance                              | UV resistant                                 |
| Special properties                            | UL standards PLTC and ITC                    |
| Ambient temperature (operation)               | -30 °C ... 75 °C (cable, fixed installation) |


## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP65                             |
|                                                                   | IP67                             |
|                                                                   | IP68                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |


## Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view


# SAC-5P-10,0-924/FS SCO - Bus system cable



1405987

<https://www.phoenixcontact.com/us/products/1405987>

Circuit diagram



Contact assignment of the M12 socket

# SAC-5P-10,0-924/FS SCO - Bus system cable



1405987

<https://www.phoenixcontact.com/us/products/1405987>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405987>

|                                                                                                                                  |                                |                                |                   |                               |
|----------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  <b>UL Listed</b><br>Approval ID: FILE E 221474 |                                |                                |                   |                               |
|                                                                                                                                  | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                            |                                |                                |                   |                               |
|                                                                                                                                  | 125 V                          | 4 A                            | -                 | -                             |

|                                                                                                                                   |                                |                                |                   |                               |
|-----------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  <b>cUL Listed</b><br>Approval ID: FILE E 221474 |                                |                                |                   |                               |
|                                                                                                                                   | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                             |                                |                                |                   |                               |
|                                                                                                                                   | 125 V                          | 4 A                            | -                 | -                             |

|                                                                                                                                          |  |  |  |  |
|------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|  <b>EAC-RoHS</b><br>Approval ID: RU D-DE.HB35.B.00387 |  |  |  |  |
|------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

# SAC-5P-10,0-924/FS SCO - Bus system cable



1405987

<https://www.phoenixcontact.com/us/products/1405987>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

## Environmental product compliance

## EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

## China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

## EU REACH SVHC

|                                     |                                                                         |
|-------------------------------------|-------------------------------------------------------------------------|
| REACH candidate substance (CAS No.) | Diazene-1,2-dicarboxamide (C,C'-azodi(formamide)) (ADCA)(CAS: 123-77-3) |
| SCIP                                | db29c6be-6128-4855-a139-23338d1df56b                                    |

## EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 9.252 kg CO2e |
|---------|---------------|