


# PT 2,5-QUATTRO-MT BU - Knife-disconnect terminal block



3211676

<https://www.phoenixcontact.com/us/products/3211676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Knife-disconnect terminal block, nom. voltage: 400 V, nominal current: 20 A, connection method: Push-in connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting: NS 35/7,5, NS 35/15, color: blue

## Your advantages

- The compact design and front connection enable wiring in a confined space
- In addition to the testing option in the double function shaft, all terminal blocks provide an additional test pick-off
- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3211676       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE22          |
| Product key                          | BE2231        |
| GTIN                                 | 4046356446495 |
| Weight per piece (including packing) | 11.26 g       |
| Weight per piece (excluding packing) | 11.26 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# PT 2,5-QUATTRO-MT BU - Knife-disconnect terminal block



3211676

<https://www.phoenixcontact.com/us/products/3211676>

## Technical data

### Product properties

|                       |                           |
|-----------------------|---------------------------|
| Product type          | Disconnect terminal block |
| Number of positions   | 1                         |
| Number of connections | 4                         |
| Number of rows        | 1                         |
| Potentials            | 1                         |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
|----------------------|-----|

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|                                                                                           |                                                              |
|-------------------------------------------------------------------------------------------|--------------------------------------------------------------|
| Number of connections per level                                                           | 4                                                            |
| Nominal cross section                                                                     | 2.5 mm <sup>2</sup>                                          |
| Connection method                                                                         | Push-in connection                                           |
| Stripping length                                                                          | 8 mm ... 10 mm                                               |
| Internal cylindrical gage                                                                 | A3                                                           |
| Connection in acc. with standard                                                          | IEC 60947-7-1                                                |
| Conductor cross-section rigid                                                             | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>                   |
| Cross section AWG                                                                         | 26 ... 12 (converted acc. to IEC)                            |
| Conductor cross-section flexible                                                          | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>                   |
| Conductor cross-section, flexible [AWG]                                                   | 26 ... 12 (converted acc. to IEC)                            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                 |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                 |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup>                                          |
| Nominal current                                                                           | 20 A                                                         |
| Maximum load current                                                                      | 20 A (with 4 mm <sup>2</sup> conductor cross-section, rigid) |
| Nominal voltage                                                                           | 400 V                                                        |
| Nominal cross section                                                                     | 2.5 mm <sup>2</sup>                                          |

### Connection cross sections directly pluggable

|                                                                   |                                              |
|-------------------------------------------------------------------|----------------------------------------------|
| Conductor cross-section rigid                                     | 0.34 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.34 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |

### Dimensions

|                 |        |
|-----------------|--------|
| Width           | 5.2 mm |
| End cover width | 2.2 mm |
| Height          | 84 mm  |

# PT 2,5-QUATTRO-MT BU - Knife-disconnect terminal block



3211676

<https://www.phoenixcontact.com/us/products/3211676>

|                    |         |
|--------------------|---------|
| Depth on NS 35/7,5 | 36.5 mm |
| Depth on NS 35/15  | 44 mm   |

## Material specifications

|                                                                         |                 |
|-------------------------------------------------------------------------|-----------------|
| Color                                                                   | blue (RAL 5015) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group                                               | I               |
| Insulating material                                                     | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 27,5 MJ/kg      |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# PT 2,5-QUATTRO-MT BU - Knife-disconnect terminal block




3211676

<https://www.phoenixcontact.com/us/products/3211676>

## Drawings

Circuit diagram



# PT 2,5-QUATTRO-MT BU - Knife-disconnect terminal block



3211676

<https://www.phoenixcontact.com/us/products/3211676>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3211676>

### DNV

Approval ID: TAE000010T



### IECEE CB Scheme

Approval ID: DE1-65861

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 400 V                 | 20 A                  | -                 | 0.2 - 2.5                   |



### EAC

Approval ID: RU C-DE.BL08.B.00644



### cULus Recognized

Approval ID: E60425

|                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| B                        |                       |                       |                   |                             |
| Only flexible conductors | 300 V                 | 20 A                  | 26 - 12           | -                           |
| Only rigid conductors    | 300 V                 | 16 A                  | 26 - 12           | -                           |
| C                        |                       |                       |                   |                             |
| Only flexible conductors | 300 V                 | 20 A                  | 26 - 12           | -                           |
| Only rigid conductors    | 300 V                 | 16 A                  | 26 - 12           | -                           |
| D                        |                       |                       |                   |                             |
|                          | 600 V                 | 5 A                   | 26 - 12           | -                           |



### LR

Approval ID: LR2371832TA



### NK

Approval ID: 14ME0912



### BV

Approval ID: 25278/C1 BV

3211676  
<https://www.phoenixcontact.com/us/products/3211676>

| keine | <div><div></div><div><b>VDE Zeichengenehmigung</b><br/>Approval ID: 40036792</div></div> |                                |                   |                               |
|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|-------------------|-------------------------------|
|       | Nominal voltage U <sub>N</sub>                                                                                                                                            | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
|       | 400 V                                                                                                                                                                     | 20 A                           | -                 | 0.2 - 2.5                     |

|                                                                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div></div><div><b>EAC</b><br/>Approval ID: KZ7500651131219505</div></div> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------|

# PT 2,5-QUATTRO-MT BU - Knife-disconnect terminal block



3211676

<https://www.phoenixcontact.com/us/products/3211676>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250108 |
| ECLASS-15.0 | 27250108 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000902 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PT 2,5-QUATTRO-MT BU - Knife-disconnect terminal block



3211676

<https://www.phoenixcontact.com/us/products/3211676>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)