

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PP-EPDM halogen-free, gray RAL 7035, Plug angled M8, coding: A, on free cable end, cable length: 1.5 m, Hygienic design, with plastic knurl

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Contamination can be detected quickly – thanks to the light color

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1406841       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF01          |
| Product key                          | AF1BCA        |
| GTIN                                 | 4046356781633 |
| Weight per piece (including packing) | 46.4 g        |
| Weight per piece (excluding packing) | 46.4 g        |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

## Technical data

### Product properties

|                      |                          |
|----------------------|--------------------------|
| Product type         | Sensor/actuator cable    |
| Application          | Food processing industry |
| Number of positions  | 4                        |
| No. of cable outlets | 1                        |
| Shielded             | no                       |
| Coding               | A                        |

### Material specifications

|                               |               |
|-------------------------------|---------------|
| Material of grip body         | PP            |
| Contact material              | CuSn          |
| Contact surface material      | Ni/Au         |
| Contact carrier material      | PP            |
| Material for screw connection | Polypropylene |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.2 Nm (M8 connectors) |
|-------------------|------------------------|

### Connector

#### Connection 1

|                     |                |
|---------------------|----------------|
| Type                | Plug angled M8 |
| Number of positions | 4              |
| Coding type         | A              |

#### Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

## Cable/line

|                                               |                                                                                                                                        |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Cable length                                  | 1.5 m                                                                                                                                  |
| Halogen-free PP gray [600]                    |                                                                                                                                        |
| Dimensional drawing                           |                                                      |
| Cable weight                                  | 23 kg/km                                                                                                                               |
| Number of positions                           | 4                                                                                                                                      |
| Shielded                                      | no                                                                                                                                     |
| Cable type                                    | Halogen-free PP gray [600]                                                                                                             |
| Conductor structure signal line               | 32x 0.10 mm                                                                                                                            |
| AWG signal line                               | 24                                                                                                                                     |
| Conductor cross section                       | 4x 0.25 mm <sup>2</sup> (Signal line)                                                                                                  |
| Wire diameter incl. insulation                | 1.17 mm ±0.02 mm (Signal line)                                                                                                         |
| External cable diameter                       | 4.50 mm ±0.15 mm                                                                                                                       |
| Outer sheath, material                        | PP-EPDM                                                                                                                                |
| External sheath, color                        | gray RAL 7035                                                                                                                          |
| Conductor material                            | Bare Cu litz wires                                                                                                                     |
| Material wire insulation                      | PP                                                                                                                                     |
| Single wire, color                            | brown, white, blue, black                                                                                                              |
| Thickness, insulation                         | ≥ 0.21 mm (Core insulation)                                                                                                            |
| Thickness, outer sheath                       | approx. 0.80 mm                                                                                                                        |
| Overall twist                                 | 4 wires, twisted                                                                                                                       |
| Length of twist, overall twist                | 44 mm                                                                                                                                  |
| Max. conductor resistance                     | 78 Ω/km (at 20 °C)                                                                                                                     |
| Insulation resistance                         | ≥ 1 GΩ*km (at 20 °C)                                                                                                                   |
| Nominal voltage, cable                        | ≤ 300 V AC                                                                                                                             |
| Test voltage                                  | ≥ 3000 V AC (Spark test)                                                                                                               |
| Minimum bending radius, fixed installation    | 5 x D                                                                                                                                  |
| Minimum bending radius, flexible installation | 10 x D                                                                                                                                 |
| Smallest bending radius, fixed installation   | 23 mm                                                                                                                                  |
| Smallest bending radius, movable installation | 45 mm                                                                                                                                  |
| Dynamic load capacity (bending)               | Max. bending cycles: 4000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Dynamic load capacity (torsion)               | Torsion: ±270 °/m, Torsion cycles: ≥4000000, Torsional frequency: max.25 Torsion cycles/min                                            |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815                                                                                               |

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

|                                 |                                                                                     |
|---------------------------------|-------------------------------------------------------------------------------------|
|                                 | in accordance with DIN EN 50267-2-1                                                 |
| Other resistance                | Resistant to cold bending and cold impacts (according to DIN EN 60811-1-4 (-40 °C)) |
| Special properties              | FDA compliant according to FDA 21 CFR 177.2600                                      |
|                                 | highly flexible                                                                     |
|                                 | Flexible cable conduit capable                                                      |
| Ambient temperature (operation) | -40 °C ... 105 °C (cable, fixed installation)                                       |
|                                 | -25 °C ... 105 °C (Cable, flexible installation)                                    |

## Environmental and real-life conditions

### Ambient conditions


|                                                                   |                                   |
|-------------------------------------------------------------------|-----------------------------------|
| Degree of protection                                              | IP65                              |
|                                                                   | IP67                              |
|                                                                   | IP68                              |
|                                                                   | IP69K                             |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 105 °C (Plug / socket) |

## Standards and regulations

|                          |                      |
|--------------------------|----------------------|
| Standard designation     | M8 connector         |
| Standards/specifications | IEC 61076-2-104      |
| Standard designation     | Material conformance |
| Standards/specifications | FDA 21 CFR 177.2600  |


## Drawings

Dimensional drawing



M8 x 1 male plug, angled version

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

Circuit diagram



Contact assignment of the M8 plug

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406841>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-4P-M 8MR/ 1,5-600 FB - Sensor/actuator cable



1406841

<https://www.phoenixcontact.com/us/products/1406841>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.447 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)