

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sensor/actuator cable, 4-position, PVC, yellow, shielded, Plug straight M12, coding: A, on  
Socket straight M12, coding: A, cable length: 1.5 m



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1409538                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF13                           |
| Product key                          | AF1IGB                         |
| GTIN                                 | 4055626017945                  |
| Weight per piece (including packing) | 123 g                          |
| Weight per piece (excluding packing) | 123 g                          |
| Customs tariff number                | 85444290                       |
| Country of origin                    | US                             |

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>

## Technical data

### Notes

|         |                                                                                                     |
|---------|-----------------------------------------------------------------------------------------------------|
| General | These cable assemblies are UL/cUL listed for use in Class I, Division 2 (CID2) hazardous locations. |
|---------|-----------------------------------------------------------------------------------------------------|

### Product properties

|                      |                                     |
|----------------------|-------------------------------------|
| Product type         | Sensor/actuator cable               |
| Application          | U.S. cables for hazardous locations |
| Number of positions  | 4                                   |
| No. of cable outlets | 1                                   |
| Shielded             | yes                                 |
| Coding               | A                                   |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Material                               | TPE-U (Locking clip)                        |
| Flammability rating according to UL 94 | HB                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |
| Outer sheath, material                 | PVC                                         |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>

## Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

## Connector

### Connection 1

|                     |                   |
|---------------------|-------------------|
| Type                | Plug straight M12 |
| Number of positions | 4                 |
| Coding type         | A                 |


### Connection 2

|                     |                     |
|---------------------|---------------------|
| Type                | Socket straight M12 |
| Number of positions | 4                   |
| Coding type         | A                   |

## Cable/line

|              |       |
|--------------|-------|
| Cable length | 1.5 m |
|--------------|-------|

### PVC yellow 105 °C [542]

|                                 |                                                                                      |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Cable weight                    | 48 kg/km                                                                             |
| UL AWM Style                    | 2517 (105 °C / 300 V)                                                                |
| Number of positions             | 4                                                                                    |
| Shielded                        | yes                                                                                  |
| Cable type                      | PVC yellow 105 °C [542]                                                              |
| Conductor structure signal line | 7x 0.25 mm                                                                           |
| AWG signal line                 | 22                                                                                   |
| Wire diameter incl. insulation  | 1.27 mm ±0.03 mm                                                                     |
| External cable diameter         | 5.50 mm ±0.2 mm                                                                      |
| Outer sheath, material          | PVC                                                                                  |
| External sheath, color          | yellow                                                                               |
| Conductor material              | Tin-plated Cu litz wires                                                             |
| Material wire insulation        | PVC                                                                                  |
| Single wire, color              | brown, blue, black, white                                                            |
| Overall twist                   | 4 wires, twisted                                                                     |
| Optical shield covering         | 85 %                                                                                 |
| Max. conductor resistance       | max. 50.5 Ω/km (20 °C)                                                               |
| Insulation resistance           | ≥ (550 M Ohms/m @ 500V)                                                              |

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>

|                                               |                                                 |
|-----------------------------------------------|-------------------------------------------------|
| Nominal voltage, cable                        | 300 V                                           |
| Minimum bending radius, flexible installation | 12 x D                                          |
| Smallest bending radius, movable installation | 66 mm                                           |
| Flame resistance                              | FT4                                             |
| Other resistance                              | UV resistant                                    |
| Special properties                            | UL standards PLTC and ITC                       |
| Ambient temperature (operation)               | -30 °C ... 105 °C (cable, fixed installation)   |
|                                               | -5 °C ... 105 °C (Cable, flexible installation) |

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP65                             |
|                                                                   | IP67                             |
|                                                                   | IP68                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |
| Ambient temperature (operation) (Locking clip)                    | -40 °C ... 65 °C (Locking clip)  |

## Approvals

### Conformity/Approvals

|                  |                                    |
|------------------|------------------------------------|
| UL, USA / Canada | Class I, Div. 2, Groups A, B, C, D |
|------------------|------------------------------------|

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>


## Drawings

Dimensional drawing



EXCLIP mounted plug

Dimensional drawing




EXCLIP mounted socket

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable

1409538

<https://www.phoenixcontact.com/us/products/1409538>

Dimensional drawing




EXCLIP plug

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable

1409538


<https://www.phoenixcontact.com/us/products/1409538>

Dimensional drawing



EXCLIP socket

Dimensional drawing




Plug, M12 x 1, straight, shielded

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable

1409538


<https://www.phoenixcontact.com/us/products/1409538>

Dimensional drawing



M12 x 1 socket, straight, shielded

Schematic diagram




Pin assignment M12 plug, 4-pos., A-coded, view plug side

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable

1409538


<https://www.phoenixcontact.com/us/products/1409538>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1409538>



### EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387



### cUL Listed

Approval ID: FILE E 359524

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 150 V                 | 4 A                   | -                 | -                           |



### UL Listed

Approval ID: FILE E 359524

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 150 V                 | 4 A                   | -                 | -                           |

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-HZ-4P-MS/1,5-542/FSSHSCOBK - Sensor/actuator cable



1409538

<https://www.phoenixcontact.com/us/products/1409538>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)