

# SACC-CI-M12FST-4CON-L180 TOR SH - Contact carrier



1418342

<https://www.phoenixcontact.com/us/products/1418342>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 4-position, Socket, straight, M12, T-coding, THR solder connection, this item is expected to be lead-free from Q4 2025 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

## Commercial data

Item number	1418342
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB23
Product key	ABQAGI
GTIN	4055626170671
Weight per piece (including packing)	7.23 g
Weight per piece (excluding packing)	3.113 g
Customs tariff number	85366990
Country of origin	DE

# SACC-CI-M12FST-4CON-L180 TOR SH - Contact carrier



1418342

<https://www.phoenixcontact.com/us/products/1418342>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	4
No. of power contacts	4
Seal present	no
Shielded	yes
Coding	T
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	63 V
Nominal current $I_N$	12 A

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Interfaces

Signal type/category	Power
----------------------	-------

### Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

### Connector

# SACC-CI-M12FST-4CON-L180 TOR SH - Contact carrier



1418342

<https://www.phoenixcontact.com/us/products/1418342>

## Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	T

## Cable/line

Signal type/category	Power
----------------------	-------

## Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C -40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad

# SACC-CI-M12FST-4CON-L180 TOR SH - Contact carrier




1418342

<https://www.phoenixcontact.com/us/products/1418342>

## Drawings

Schematic diagram



Pin assignment of M12 socket, 4-pos., T-coded, socket side view

# SACC-CI-M12FST-4CON-L180 TOR SH - Contact carrier



1418342

<https://www.phoenixcontact.com/us/products/1418342>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1418342>

<b>cUL Recognized</b> Approval ID: E468743-20190917				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	63 V	12 A	16	-

<b>UL Recognized</b> Approval ID: E468743-20190917				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	63 V	12 A	16	-

# SACC-CI-M12FST-4CON-L180 TOR SH - Contact carrier



1418342

<https://www.phoenixcontact.com/us/products/1418342>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 9.0	EC003557
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M12FST-4CON-L180 TOR SH - Contact carrier



1418342

<https://www.phoenixcontact.com/us/products/1418342>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2848dbcc-40cc-482b-9a8b-2dc75e4158e9

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)