

BL2 BPC 1541E-8/64 US IG 01 - Box PC



1436817

<https://www.phoenixcontact.com/us/products/1436817>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Atom® E3940 processor, with Ubuntu Desktop and ready-to-install Ignition visualization software

Commercial data

Item number	1436817
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBABA
GTIN	4063151814205
Weight per piece (including packing)	934 g
Weight per piece (excluding packing)	762 g
Customs tariff number	84715000
Country of origin	TW

Technical data

Product properties

Product type	Box PC
--------------	--------

Computer data

Processor	Intel® Atom™ E3940 1.6 GHz
Operating system	Ubuntu 22.04
RAM	8 GB LPDDR4
Data storage system	64 GB M.2-SSD
Cooling	passive

Display

Display type	none
--------------	------

Connection data

Power supply

Connection method	Screw connection
Conductor cross-section, rigid	0.14 mm² ... 1.5 mm²
Conductor cross-section, flexible	0.14 mm² ... 1.5 mm²
Conductor cross-section AWG	28 ... 16
Stripping length	7 mm

Interfaces

Interfaces	1x DP++
	2x USB 3.0
	2x COM ports
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

Dimensions

External dimensions

Width / Height / Depth	99 mm / 92 mm / 63 mm
------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

BL2 BPC 1541E-8/64 US IG 01 - Box PC



1436817

<https://www.phoenixcontact.com/us/products/1436817>

FCC

Title 47 Part 15 Subpart B:2018 Class A

1436817

<https://www.phoenixcontact.com/us/products/1436817>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1436817>



IECEE CB Scheme
Approval ID: US-39601-M1-UL



UL Listed
Approval ID: E238705 D12:D1050



cUL Listed
Approval ID: E238705 D12:D1050

1436817

<https://www.phoenixcontact.com/us/products/1436817>

Classifications

ECLASS

ECLASS-13.0	19200102
ECLASS-15.0	19200102

ETIM

ETIM 9.0	EC001413
----------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)