

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 6.2 mm, Number of individual labels: 60, text field height: 5.45 mm, text field width: 5.2 mm

Your advantages

- The UCT1-TMF ... UniCard labeling range includes markers for Weidmüller, Wago, ABB (entrelec), Conta-Clip, and Klemsan terminal blocks
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0829724                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8118                         |
| GTIN                                 | 4046356598774                  |
| Weight per piece (including packing) | 11.319 g                       |
| Weight per piece (excluding packing) | 10.73 g                        |
| Country of origin                    | PL                             |

# UCT1-TMF 6 CUS - Marker for terminal blocks



0829724

<https://www.phoenixcontact.com/us/products/0829724>

## Technical data

### Notes

|         |                                     |
|---------|-------------------------------------|
| General | Can be labeled via thermal transfer |
|---------|-------------------------------------|

### Product properties

|              |               |
|--------------|---------------|
| Product type | Klemmenmarker |
| Pitch        | 6.2 mm        |

### Marking

|                                     |                                       |
|-------------------------------------|---------------------------------------|
| Number of individual labels         | 60                                    |
| Number of individual labels per row | 10                                    |
| Identification technology           | Thermal transfer for sheets and cards |

### Dimensions

|        |         |
|--------|---------|
| Width  | 5.45 mm |
| Height | 5.20 mm |
| Depth  | 2.40 mm |
| Pitch  | 6.2 mm  |
| Length | 5.2 mm  |

### Material specifications

|                                                        |                                |
|--------------------------------------------------------|--------------------------------|
| Color                                                  | white (RAL 9010)               |
| Material                                               | PC                             |
| Flammability rating according to UL 94                 | V0                             |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3                    |
| Components                                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Test for substances that would hinder coating with paint or varnish

|               |                                |
|---------------|--------------------------------|
| Result        | Test passed                    |
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

#### Tesa film test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

#### UV resistance

# UCT1-TMF 6 CUS - Marker for terminal blocks



0829724

<https://www.phoenixcontact.com/us/products/0829724>

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |
| Procedure     | Artificial irradiation.        |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 100 °C (121 °C) | Test passed                     |

## Wipe resistance of inscriptions

|                                                   |                                                                                        |
|---------------------------------------------------|----------------------------------------------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                    | Test passed                                                                            |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                                                            |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                                                            |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                                                            |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                                                            |
| Specification                                     | ISO 175:2010 (following)                                                               |
| Test duration                                     | 168 h                                                                                  |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                                                            |
| IRM 901                                           | Test passed                                                                            |
| IRM 902                                           | Test passed                                                                            |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C                                                               |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 2 years                                                                         |

# UCT1-TMF 6 CUS - Marker for terminal blocks



0829724

<https://www.phoenixcontact.com/us/products/0829724>

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |                              |
|---------------|------------------------------|
| Mounting type | snap into flat marker groove |
|---------------|------------------------------|

## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

# UCT1-TMF 6 CUS - Marker for terminal blocks



0829724

<https://www.phoenixcontact.com/us/products/0829724>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000761 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UCT1-TMF 6 CUS - Marker for terminal blocks



0829724  
<https://www.phoenixcontact.com/us/products/0829724>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |
| EF3.0 Climate Change                    |                            |
| CO2e kg                                 | 0.047 kg CO2e              |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)