

# IV-AW3P-1939 - Terminal position assurance

1521029

<https://www.phoenixcontact.com/us/products/1521029>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal position assurance, number of positions: 3, material: PA-GF



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1521029       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BF72          |
| Product key                          | AF2IEC        |
| GTIN                                 | 4063151985431 |
| Weight per piece (including packing) | 22.22 g       |
| Weight per piece (excluding packing) | 0.43 g        |
| Country of origin                    | MX            |

# IV-AW3P-1939 - Terminal position assurance

1521029

<https://www.phoenixcontact.com/us/products/1521029>



## Technical data

### Notes

|                   |  |
|-------------------|--|
| General           | AW3P-1939  |
| General           | Use with AT04-3P-1939 housings   |
| Trade restriction |  |
| CE note           | The products are offered exclusively for export outside the EU and the European Economic Area. |


### Product properties

|                     |                             |
|---------------------|-----------------------------|
| Product type        | Terminal position assurance |
| Series              | AT04                        |
| Number of positions | 3                           |

### Electrical properties

|                       |                         |
|-----------------------|-------------------------|
| Nominal voltage $U_N$ | 50 V AC/DC (IEC rating) |
|-----------------------|-------------------------|

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 7.8 mm   |
| Height              | 7 mm   |
| Length              | 20 mm  |

### Material specifications

|                  |       |
|------------------|-------|
| Housing material | PA-GF |
|------------------|-------|

### Environmental and real-life conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient conditions              |                   |
| Ambient temperature (operation) | -55 °C ... 125 °C |

# IV-AW3P-1939 - Terminal position assurance


1521029

<https://www.phoenixcontact.com/us/products/1521029>



## Drawings

Dimensional drawing



AW3P-1939 top view and side view

# IV-AW3P-1939 - Terminal position assurance

1521029

<https://www.phoenixcontact.com/us/products/1521029>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

# IV-AW3P-1939 - Terminal position assurance

1521029

<https://www.phoenixcontact.com/us/products/1521029>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)