

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable



1010673

<https://www.phoenixcontact.com/us/products/1010673>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, POC halogen-free, irradiated, black RAL 9005, Plug straight M12, coding: B, on Socket straight M12, coding: B, cable length: 0.2 m

Commercial data

Item number	1010673
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CJA
GTIN	4055626484891
Weight per piece (including packing)	47.5 g
Weight per piece (excluding packing)	47.5 g
Country of origin	PL

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable



1010673

<https://www.phoenixcontact.com/us/products/1010673>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	4
No. of cable outlets	1

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M12
Number of positions	4
Coding type	B

Connection 2

Type	Socket straight M12
Number of positions	4
Coding type	B

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable



1010673

<https://www.phoenixcontact.com/us/products/1010673>

Cable/line

Cable length	0.2 m
POC irradiated halogen-free black [BF 145]	
Cable weight	86 kg/km
Number of positions	5
Shielded	yes
Cable type	POC irradiated halogen-free black [BF 145]
AWG signal line	20
Conductor cross section	5x 0.5 mm ²
Wire diameter incl. insulation	1.9 mm
External cable diameter	7.30 mm
Outer sheath, material	POC
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	POC
Single wire, color	black 1, black 2, black 3, black 4, black 5
Overall twist	5 wires around filler to the core
Nominal voltage, cable	300 V
Test voltage Core/Core	3500 V
Test voltage Core/Shield	2500.00 V
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	12 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	88 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 10 x D, Traversing path: 5 m, Traversing rate: 4 m/s, Acceleration: 5 m/s ²
Halogen-free	according to IEC 60754-1 in accordance with DIN EN 50267-2-1
Flame resistance	IEC 60332-1 According to DIN EN 50265-2-1
Concentration of fumes	in accordance with IEC 61034 EN 50268-2
Other resistance	Good resistance to aggressive media
Special properties	Irradiated
Ambient temperature (operation)	-55 °C ... 145 °C (cable, fixed installation) -35 °C ... 120 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable



1010673

<https://www.phoenixcontact.com/us/products/1010673>

Ambient temperature (operation) (Cable, fixed installation)	-25 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-5 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable

1010673

<https://www.phoenixcontact.com/us/products/1010673>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, angled, shielded

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable

1010673

<https://www.phoenixcontact.com/us/products/1010673>

Schematic diagram




Pin assignment M12 plug, 4-pos., A-coded, view plug side

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable

1010673


<https://www.phoenixcontact.com/us/products/1010673>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable



1010673

<https://www.phoenixcontact.com/us/products/1010673>

Classifications

ECLASS

ECLASS-13.0

27060311

ETIM

ETIM 8.0

EC001855

UNSPSC

UNSPSC 21.0

26121600

SAC-4P-M12MSB/0,2-BF145/FRB SH - Sensor/actuator cable



1010673

<https://www.phoenixcontact.com/us/products/1010673>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com