

# PABA WH/23 - Insert label

1013779

<https://www.phoenixcontact.com/us/products/1013779>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, Strip, white, unmarked, can be labeled with: CMS-P1-PLOTTER, cable diameter range: 1.5 ... 35 mm, mounting type: slide-on, Number of individual labels: 20, text field height: 4 mm, text field width: 23 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1013779       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG20          |
| Product key                          | BG2213        |
| GTIN                                 | 4017918013967 |
| Weight per piece (including packing) | 8.1 g         |
| Weight per piece (excluding packing) | 5.69 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | CN            |

## Technical data

### Notes

|         |                         |
|---------|-------------------------|
| General | Can be labeled with CMS |
|---------|-------------------------|

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|                                     |    |
|-------------------------------------|----|
| Number of individual labels         | 20 |
| Number of individual labels per row | 1  |

### Dimensions

|        |          |
|--------|----------|
| Width  | 23.08 mm |
| Height | 4.07 mm  |
| Depth  | 1.89 mm  |

### Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | white (RAL 9010) |
| Flammability rating according to UL 94 | V0               |
| Base element material                  | ABS              |

### Cable/line

|                         |                  |
|-------------------------|------------------|
| External cable diameter | 1.5 mm ... 35 mm |
|-------------------------|------------------|

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|               |                                       |
|---------------|---------------------------------------|
| Result        | Test passed                           |
| Specification | DIN EN ISO 1518-1:2019-10 (following) |
| Requirements  | ≥ 5 N                                 |
| Result        | Test passed                           |

#### Tesafilm test

|               |                                  |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
| Result        | Test passed                      |

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |
| Procedure     | Artificial irradiation.        |

#### Temperature resistance

|               |                                 |
|---------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h                           |

# PABA WH/23 - Insert label



1013779

<https://www.phoenixcontact.com/us/products/1013779>

|                       |             |
|-----------------------|-------------|
| Rating 80 °C (105 °C) | Test passed |
|-----------------------|-------------|

## Wipe resistance of inscriptions

|                                                   |                                                |
|---------------------------------------------------|------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                                   | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                    | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Specification                                     | ISO 175:2010 (following)                       |
| Test duration                                     | 168 h                                          |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                    |
| IRM 901                                           | Test passed                                    |
| IRM 902                                           | Test passed                                    |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -15 °C ... 65 °C                                                                |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

## Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# PABA WH/23 - Insert label


1013779

<https://www.phoenixcontact.com/us/products/1013779>



## Drawings

Dimensional drawing



# PABA WH/23 - Insert label

1013779

<https://www.phoenixcontact.com/us/products/1013779>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# PABA WH/23 - Insert label



1013779  
<https://www.phoenixcontact.com/us/products/1013779>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |
| EF3.0 Climate Change                    |                            |
| CO2e kg                                 | 0.046 kg CO2e              |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)