

# RC-07S1N121500 - Cable connector

1594566

<https://www.phoenixcontact.com/us/products/1594566>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 7, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N, this item is expected to be lead-free from Q4 2025 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1594566
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFA
GTIN	4046356202152
Weight per piece (including packing)	82.9 g
Weight per piece (excluding packing)	77.8 g
Customs tariff number	85366990
Country of origin	DE

# RC-07S1N121500 - Cable connector



1594566

<https://www.phoenixcontact.com/us/products/1594566>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	7
Direction of rotation	Standard
Connection profile	7
Number Contact (Contact group 1)	7
Diameter Contact (Contact group 1)	2 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm <sup>2</sup>
Litz wire cross-section max. Contact (Contact group 1)	2.5 mm <sup>2</sup>
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overshoot category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	Pg9
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67
	IP68

### Environmental and real-life conditions

# RC-07S1N121500 - Cable connector

1594566

<https://www.phoenixcontact.com/us/products/1594566>



## Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

# RC-07S1N121500 - Cable connector


1594566

<https://www.phoenixcontact.com/us/products/1594566>



## Drawings

Schematic diagram



Connector pin assignment


# RC-07S1N121500 - Cable connector

1594566

<https://www.phoenixcontact.com/us/products/1594566>



Schematic diagram



Connector pin assignment


## RC-07S1N121500 - Cable connector

1594566

<https://www.phoenixcontact.com/us/products/1594566>

**PHÖNIX CONTACT**

## Schematic diagram



## Dimensional drawing

# RC-07S1N121500 - Cable connector

1594566

<https://www.phoenixcontact.com/us/products/1594566>



## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-07S1N121500 - Cable connector

1594566

<https://www.phoenixcontact.com/us/products/1594566>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	329e0776-90d8-4bb3-b31d-d17d131e8110

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)