

# FP 0,8/ 32-MV 1,15 - SMD male connectors




1061728

<https://www.phoenixcontact.com/us/products/1061728>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

SMD male connector, nominal current: 1.7 A, test voltage: 500 V AC, number of positions: 32, pitch: 0.8 mm, color: black, contact surface: Au, contact connection type: Pin, mounting: SMD soldering



## Your advantages

- Gold-plated contacts ensure transfer quality remains stable over the long term
- Reliable mechanical and electrical connections, thanks to the double-sided ScaleX contact system
- Robustness: ScaleX technology for high tolerance compensation and protection of contacts
- Flexible device design: various numbers of positions, designs, and stack heights with high wipe lengths

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1061728       |
| Packing unit                         | 500 pc        |
| Minimum order quantity               | 500 pc        |
| Sales key                            | AA23          |
| Product key                          | AAWGDB        |
| GTIN                                 | 4055626717203 |
| Weight per piece (including packing) | 2.142 g       |
| Weight per piece (excluding packing) | 0.65 g        |
| Customs tariff number                | 85366930      |
| Country of origin                    | CN            |

# FP 0,8/ 32-MV 1,15 - SMD male connectors



1061728

<https://www.phoenixcontact.com/us/products/1061728>

## Technical data

### Product properties

|                     |                     |
|---------------------|---------------------|
| Product type        | SMD male connector  |
| Product family      | FP 0,8/...-MV 1,15  |
| Number of positions | 32                  |
| Pitch               | 0.8 mm              |
| Number of rows      | 2                   |
| Pin layout          | Linear pad geometry |

### Electrical properties

#### Properties

|                       |                                               |
|-----------------------|-----------------------------------------------|
| Nominal current $I_N$ | 1.7 A IEC 60512-5-2:2002-02 (at 20°C 52-pos.) |
| Contact resistance    | 25 mΩ                                         |
| Test voltage          | 500 V AC IEC 60512-4-1:2003-05                |

#### Data transmission

|                        |         |
|------------------------|---------|
| Data transmission rate | 16 Gbps |
|------------------------|---------|

### Mounting

|               |                     |
|---------------|---------------------|
| Mounting type | SMD soldering       |
| Pin layout    | Linear pad geometry |

#### Processing notes

|                                  |                  |
|----------------------------------|------------------|
| Process                          | Reflow soldering |
| Moisture Sensitive Level         | MSL 1            |
| Classification temperature $T_c$ | 260 °C           |
| Solder cycles in the reflow      | 3                |

### Material specifications

#### Material data - contact

|                                             |                                                                                  |
|---------------------------------------------|----------------------------------------------------------------------------------|
| Note                                        | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                            | Cu alloy                                                                         |
| Surface characteristics                     | Selective coating                                                                |
| Metal surface contact area (top layer)      | Gold (Au)                                                                        |
| Metal surface contact area (middle layer)   | Nickel (Ni)                                                                      |
| Metal surface soldering area (top layer)    | Tin (Sn)                                                                         |
| Metal surface soldering area (middle layer) | Nickel (Ni)                                                                      |

#### Material data - housing

|                           |              |
|---------------------------|--------------|
| Color (Housing)           | black (9005) |
| Insulating material       | LCP          |
| Insulating material group | IIIb         |

# FP 0,8/ 32-MV 1,15 - SMD male connectors



1061728


<https://www.phoenixcontact.com/us/products/1061728>

|                                        |     |
|----------------------------------------|-----|
| CTI according to IEC 60112             | 150 |
| Flammability rating according to UL 94 | V0  |

## Notes

|                                 |                                                                                                                                                                                                                      |
|---------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation              | The permissible voltage during operation depends on the application, taking into consideration the air clearances and creepage distances within the scope of insulation requirements in accordance with IEC 60664-1. |
| Details for soldering processes | The items are suitable for assembly on both sides and for overhead soldering.                                                                                                                                        |

## Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 0.8 mm                                                                             |
| Width [w]           | 16.7 mm                                                                            |
| Height [h]          | 6.25 mm                                                                            |
| Length [l]          | 6.1 mm                                                                             |
| Installed height    | 5.65 mm                                                                            |

## Application

|                                            |                                                                                      |
|--------------------------------------------|--------------------------------------------------------------------------------------|
| Contact cover                              | 0.8 mm                                                                               |
| Center offset                              | ± 0.7 mm in longitudinal and transverse direction                                    |
| Stack height                               | 6 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-FV 4,85)   |
|                                            | 9 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-FV 7,85)   |
|                                            | 12 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-FV 10,85) |
| Wipe length                                | 1.5 mm                                                                               |
| Angular tolerance                          | ± 5 ° in longitudinal and transverse direction (when plugging in)                    |
|                                            | ± 5 ° in longitudinal and transverse direction (when plugged in)                     |
| Axial offset in X direction (longitudinal) | ± 0.3 mm (Tolerance compensation when plugged in)                                    |
| Axial offset in Y direction (transversal)  | ± 0.3 mm (Tolerance compensation when plugged in)                                    |

## PCB design

|              |              |
|--------------|--------------|
| Pad geometry | 0.5 x 2.4 mm |
|--------------|--------------|

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-2:2002-02 |
| Tested number of positions | 80                    |

### Insulation resistance

# FP 0,8/ 32-MV 1,15 - SMD male connectors



1061728

<https://www.phoenixcontact.com/us/products/1061728>

|                                              |                          |
|----------------------------------------------|--------------------------|
| Specification                                | IEC 60512-3-1:2002-02    |
| Insulation resistance, neighboring positions | $\geq 5 \text{ G}\Omega$ |

## Air clearances and creepage distances |

|                                                   |         |
|---------------------------------------------------|---------|
| Insulating material group                         | IIIb    |
| Minimum value for clearance and creepage distance | 0.25 mm |

## Environmental and real-life conditions

### Vibration test

|                        |                                          |
|------------------------|------------------------------------------|
| Specification          | IEC 60068-2-6:2007-12                    |
| Frequency              | 10 - 2000 - 10 Hz                        |
| Sweep speed            | 1 octave/min                             |
| Amplitude              | 1.5 mm (10 Hz ... 58 Hz)                 |
| Acceleration           | 200 m/s <sup>2</sup> (58 Hz ... 2000 Hz) |
| Test duration per axis | 2.5 h                                    |
| Test directions        | X-, Y- and Z-axis                        |

### Durability test

|                                              |                                   |
|----------------------------------------------|-----------------------------------|
| Specification                                | IEC 60512-9-1:2010-03 (following) |
| Impulse withstand voltage at sea level       | 0.8 kV                            |
| Contact resistance R <sub>1</sub>            | 25 m $\Omega$                     |
| Contact resistance R <sub>2</sub>            | 25 m $\Omega$                     |
| Insertion/withdrawal cycles                  | 500                               |
| Insulation resistance, neighboring positions | $\geq 5 \text{ G}\Omega$          |

### Climatic test

|                                   |                        |
|-----------------------------------|------------------------|
| Specification                     | IEC 60512-11-7:2003-05 |
| Corrosive stress                  | Method 1, 10 days      |
| Power-frequency withstand voltage | 500 V AC               |

### Shocks

|                 |                                   |
|-----------------|-----------------------------------|
| Specification   | IEC 60068-2-27:2008-02            |
| Pulse shape     | Semi-sinusoidal                   |
| Acceleration    | 490 m/s <sup>2</sup>              |
| Shock duration  | 11 ms                             |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

### Ambient conditions

|                                         |                   |
|-----------------------------------------|-------------------|
| Ambient temperature (operation)         | -55 °C ... 125 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C  |
| Relative humidity (storage/transport)   | 30 % ... 70 %     |
| Ambient temperature (assembly)          | -5 °C ... 100 °C  |


## Packaging specifications

# FP 0,8/ 32-MV 1,15 - SMD male connectors




1061728

<https://www.phoenixcontact.com/us/products/1061728>

|                             |                                                                                    |
|-----------------------------|------------------------------------------------------------------------------------|
| Dimensional drawing         |  |
| Type of packaging           | 16 mm wide tape                                                                    |
| [W] tape width              | 16 mm                                                                              |
| [W2] coil overall dimension | ≤ 330 mm                                                                           |
| [A] coil diameter           | ≤ 22.4 mm                                                                          |
| Outer packaging type        | Transparent-Bag                                                                    |


## Drawings

Diagram




Type: FP 0,8/...-MV 1,15 with FP 0,8/...-FV 4,85

Diagram




Type: FP 0,8/...-MV 1,15 with FP 0,8/...-FV 7,85 – contacts

Diagram



Type: FP 0,8/...-MV 1,15 with FP 0,8/...-FV 10,85 – contacts

Diagram



Type: FP 0,8/...-MV 1,15 with FP 0,8/...-FV 10,85 – shielding plate

# FP 0,8/ 32-MV 1,15 - SMD male connectors



1061728

<https://www.phoenixcontact.com/us/products/1061728>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1061728>



**cULus Recognized**

Approval ID: E118976-20190703

# FP 0,8/ 32-MV 1,15 - SMD male connectors



1061728

<https://www.phoenixcontact.com/us/products/1061728>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# FP 0,8/ 32-MV 1,15 - SMD male connectors



1061728

<https://www.phoenixcontact.com/us/products/1061728>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)