

STEP-BAT/LI-ION/18.5DC/46WH - Battery module



1081355

<https://www.phoenixcontact.com/us/products/1081355>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Battery module (device with battery), lithium-ion, 18.5 V DC, 46 Wh



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1081355 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CM20 |
| Product key | CMUSL9 |
| GTIN | 4055626809427 |
| Weight per piece (including packing) | 333 g |
| Weight per piece (excluding packing) | 293 g |
| Customs tariff number | 85076000 |
| Country of origin | DE |

Technical data

Notes

General

| | |
|---------------------|--|
| Note on the battery | This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the technical data area under "Latest startup". To prevent deep discharge, store and transport the battery module outside of the uninterruptible power supply. |
|---------------------|--|

Input data

| | |
|---------------|-----------|
| Input voltage | 18.5 V DC |
|---------------|-----------|

Output data

| | |
|------------------------------|-----|
| Balancer circuit, internal | yes |
| Protective circuit, internal | yes |

Energy storage

| | |
|---|-----------------------------|
| End-of-charge voltage | 21 V DC |
| Charging current | 400 mA |
| Nominal capacity | 2.5 Ah |
| Battery module service life, cyclically | > 500 (Full cycles) |
| Latest startup date (battery only) | 12 Months (20 °C ... 30 °C) |
| Battery technology | Lithium-ion |
| Memory medium | LI-ION, 46 Wh |
| Number of cells | 5 |
| Size designation | Block |
| Battery pack | yes |
| IQ technology | no |
| Suitable for fast charging | no |

Product properties

| | |
|----------------|--------------------------------------|
| Product type | Battery module |
| Product family | Battery module (device with battery) |
| IQ technology | no |

Insulation characteristics

| | |
|---------------------|-----|
| Protection class | III |
| Degree of pollution | 2 |

Dimensions

| | |
|--------|-------|
| Width | 88 mm |
| Height | 46 mm |
| Depth | 61 mm |

STEP-BAT/LI-ION/18.5DC/46WH - Battery module



1081355

<https://www.phoenixcontact.com/us/products/1081355>

Environmental and real-life conditions

Ambient conditions

| | |
|--|--------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | 0 °C ... 40 °C |
| Ambient temperature (storage/transport) | -20 °C ... 45 °C |
| Max. permissible relative humidity (operation) | ≤ 95 % (25 °C, non-condensing) |

Ex data

| | |
|----------------------------|----|
| Suited for EX-applications | no |
|----------------------------|----|

STEP-BAT/LI-ION/18.5DC/46WH - Battery module

1081355

<https://www.phoenixcontact.com/us/products/1081355>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1081355>



IECEE CB Scheme

Approval ID: DK-123700-UL



cULus Recognized

Approval ID: MH48963



cULus Recognized

Approval ID: MH48963



EAC

Approval ID: RU S-DE.BL08.W.00764

STEP-BAT/LI-ION/18.5DC/46WH - Battery module

1081355

<https://www.phoenixcontact.com/us/products/1081355>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27050403 |
| ECLASS-15.0 | 27050403 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003893 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26111700 |
|-------------|----------|

STEP-BAT/LI-ION/18.5DC/46WH - Battery module

1081355

<https://www.phoenixcontact.com/us/products/1081355>



Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(c)-I |

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-25 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | df2129b8-5e2f-45bc-bc92-a694c7af8fd6 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com