

# IPD P 3P2,5 M GY - Connector



1088671

<https://www.phoenixcontact.com/us/products/1088671>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, connection method: Push-lock connection, number of positions: 2+PE, Pin, 0.5 mm<sup>2</sup> .. 2.5 mm<sup>2</sup>, 500 V, 20 A, PA, light gray, coding: P, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm

## Your advantages

- Easy distribution of power, as components are plugged directly
- Simple, time-saving wiring in the field with Push-Lock connection
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system
- Secure, tool-free locking even in particularly difficult installation situations
- Fast commissioning with preassembled cable assemblies

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1088671       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF51          |
| Product key                          | AF6JAA        |
| GTIN                                 | 4055626890883 |
| Weight per piece (including packing) | 48.4 g        |
| Weight per piece (excluding packing) | 48.4 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# IPD P 3P2,5 M GY - Connector

1088671

<https://www.phoenixcontact.com/us/products/1088671>



## Technical data

### Notes

#### General

**NOTE:** Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

### Product properties

|                                    |                        |
|------------------------------------|------------------------|
| Product type                       | Installation connector |
| Product family                     | IPD                    |
| Number of positions                | 3                      |
| Connection profile                 | 2+PE                   |
| Position marking                   | L, N, PE               |
| Number of connections per position | 1                      |
| Coding                             | P                      |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                             |          |
|-----------------------------|----------|
| Rated surge voltage (III/3) | 6 kV     |
| Rated current               | 20 A     |
| Rated voltage (III/3)       | 500 V    |
| Nominal voltage $U_N$       | 500 V AC |
|                             | 500 V DC |
| Nominal current $I_N$       | 20 A     |

### Connection data

#### Connection technology


|                                     |                      |
|-------------------------------------|----------------------|
| Connection method On the field side | Push-lock connection |
|-------------------------------------|----------------------|

#### Conductor connection

|                                      |                                             |
|--------------------------------------|---------------------------------------------|
| Conductor cross section flexibel     | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section solid        | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section with ferrule | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Connection cross section AWG         | 20 ... 14                                   |

### Dimensions

#### Dimensional drawing



# IPD P 3P2,5 M GY - Connector



1088671

<https://www.phoenixcontact.com/us/products/1088671>

|        |         |
|--------|---------|
| Width  | 26.5 mm |
| Height | 26.9 mm |
| Length | 85.9 mm |

## Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color (Housing)                        | light gray (RAL 7035) |
| Material Housing                       | PA                    |
| Material Seal                          | NBR                   |
| Flammability rating according to UL 94 | V0                    |
| Contact material                       | Cu                    |
| Contact surface material               | Ni/Ag/Sn              |

## Cable/line

|                         |                |
|-------------------------|----------------|
| External cable diameter | 6 mm ... 9 mm  |
|                         | 8 mm ... 13 mm |
| Position marking        | L, N, PE       |

## Mechanical properties

### Mechanical data

|                             |                      |
|-----------------------------|----------------------|
| Insertion/withdrawal cycles | 50 (IP66/IP68/IP69K) |
|                             | 100 (IP66)           |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                                        |
|-----------------------------------------|----------------------------------------|
| Degree of protection                    | IP66                                   |
|                                         | IP68 (2 m / 24 h)                      |
|                                         | IP69K                                  |
|                                         | Touch-proof when not plugged in (IP2X) |
| Impact strength                         | IK07                                   |
| Ambient temperature (operation)         | -30 °C ... 100 °C                      |
| Temperature when conductor connected    | -5 °C ... 50 °C                        |
| Ambient temperature (storage/transport) | -30 °C ... 100 °C                      |
| Resistance to UV radiation              | yes                                    |

# IPD P 3P2,5 M GY - Connector


1088671

<https://www.phoenixcontact.com/us/products/1088671>




## Drawings


Dimensional drawing




Diagram



Derating diagram for 1.0 mm<sup>2</sup>



Derating diagram for 1.5 mm<sup>2</sup>



Derating diagram for 2.5 mm<sup>2</sup>

# IPD P 3P2,5 M GY - Connector



1088671

<https://www.phoenixcontact.com/us/products/1088671>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1088671>



### VDE Zeichengenehmigung

Approval ID: 40059408



### cULus Listed

Approval ID: E468743

|                             | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-----------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine                       |                       |                       |                   |                             |
| Only rigid conductors       | 600 V                 | 20 A                  | - 14              | -                           |
| multi-stranded with ferrule | 600 V                 | 20 A                  | - 14              | -                           |
| Only flexible conductors    | 600 V                 | 20 A                  | - 14              | -                           |

# IPD P 3P2,5 M GY - Connector



1088671

<https://www.phoenixcontact.com/us/products/1088671>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440605 |
| ECLASS-15.0 | 27440605 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002560 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# IPD P 3P2,5 M GY - Connector



1088671

<https://www.phoenixcontact.com/us/products/1088671>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)