


1694172

<https://www.phoenixcontact.com/us/products/1694172>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket angled M8, coding: A, cable length: 10 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components

Commercial data

Item number	1694172
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF01
Product key	AF1BCA
GTIN	4017918177171
Weight per piece (including packing)	218 g
Weight per piece (excluding packing)	183.118 g
Customs tariff number	85444290
Country of origin	DE

SAC-4P-10,0-PUR/M 8FR - Sensor/actuator cable



1694172

<https://www.phoenixcontact.com/us/products/1694172>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.2 Nm (M8 connectors)
-------------------	------------------------

Connector

Connection 1

SAC-4P-10,0-PUR/M 8FR - Sensor/actuator cable



1694172

<https://www.phoenixcontact.com/us/products/1694172>

Type	free cable end
------	----------------


Connection 2

Type	Socket angled M8
Number of positions	4
Coding type	A

Cable/line

Cable length	10 m
--------------	------

PUR halogen-free black [PUR]

Dimensional drawing		
Cable weight	23 kg/km	
UL AWM Style	20549 / 10493 (80°C/300 V)	
Number of positions	4	
Shielded	no	
Cable type	PUR halogen-free black [PUR]	
Conductor structure signal line	32x 0.10 mm	
AWG signal line	24	
Conductor cross section	4x 0.25 mm ² (Signal line)	
Wire diameter incl. insulation	1.17 mm ±0.02 mm (Signal line)	
External cable diameter	3.95 mm ±0.15 mm	
Outer sheath, material	PUR	
External sheath, color	black-gray RAL 7021	
Conductor material	Bare Cu litz wires	
Material wire insulation	PP	
Single wire, color	brown, white, blue, black	
Thickness, insulation	≥ 0.21 mm (Core insulation)	
	approx. 0.50 mm (Outer cable sheath)	
Overall twist	4 wires, twisted	
Max. conductor resistance	max. 78 Ω/km (at 20 °C)	
Insulation resistance	≥ 100 GΩ*km (at 20 °C)	
Nominal voltage, cable	≤ 300 V	
Test voltage	≥ 3000 V	
Smallest bending radius, fixed installation	20 mm	
Smallest bending radius, movable installation	40 mm	
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 44 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 5	

SAC-4P-10,0-PUR/M 8FR - Sensor/actuator cable



1694172

<https://www.phoenixcontact.com/us/products/1694172>

	m/s ²
Dynamic load capacity (torsion)	Torsion: $\pm 180^\circ/\text{m}$, Torsion cycles: ≥ 20000000 , Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP65 IP67 IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

Standards and regulations

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104


Drawings

Dimensional drawing



Socket M8 x 1, angled

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side


SAC-4P-10,0-PUR/M 8FR - Sensor/actuator cable

1694172

<https://www.phoenixcontact.com/us/products/1694172>




Schematic diagram



Layout of connector pin assignments

Circuit diagram



Contact assignment of M8 socket

SAC-4P-10,0-PUR/M 8FR - Sensor/actuator cable



1694172

<https://www.phoenixcontact.com/us/products/1694172>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1694172>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	4 A	-	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387				
--	--	--	--	--

SAC-4P-10,0-PUR/M 8FR - Sensor/actuator cable



1694172

<https://www.phoenixcontact.com/us/products/1694172>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-10,0-PUR/M 8FR - Sensor/actuator cable



1694172

<https://www.phoenixcontact.com/us/products/1694172>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	2.565 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com